

PRODUCT NUMBER
71991-XXXXLF

ROHS COMPATIBLE, SEE NOTE 6.

OPTIONAL LETTER

H: HIGH TEMPERATURE PRODUCT.

NUMBER OF POSITIONS PER ROW: 02 TO 50.

PLATING CODE

3= 0.76µm GOLD ON CONTACT AREA.




2µm MIN MATTE TIN ON TAIL.

4= 2µm MIN MATTE TIN FULL PLATED

8= 0.38µm GOLD ON CONTACT AREA.

2µm MIN MATTE TIN ON TAIL.

1.27µm Ni MIN UNDERPLATING



NOTES:

1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0

LOW TEMPERATURE: COLOR BLUE

HIGH TEMPERATURE: COLOR GREY.

2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.

3 - 2 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.

4 - TO DETERMINE DIMENSIONS:

N = NUMBER OF POSITIONS PER ROW

EXAMPLE: 8 POS: (Nx2.54)-0.08=20.24 mm

5 - RECOMMENDED IR PROFIL PER TA 842.

6 - ROHS COMPATIBLE PRODUCT SPECIFICATIONS

d - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004

7 - END STAND-OFFS FOR 2x2 UP TO 2x5 POS

NO END STAND-OFFS FOR 2x6 UP TO 2x50 POS

NOTE 7

mat'l. code		SEE NOTES			surface	tolerance	projection	product family
lfr	ecm no	dr	date	ISO 1302	ISO 406	ISO 1101		DUBOX
Y	B-19123	LMU	14.10.20	tolerances unless otherwise specified <td></td> <td></td> <td></td> <td></td>				
T	F06-0137	DLE	06.02.27	angles	linear	±0.3		
U	F06-0204	DLE	06.06.20	dr	D	LEGRAND		
V	F06-0323	DLE	06.11.21	lengr	P	NIZZI		
W	F09-0011	LMU	09.02.16	chr	D	LEGRAND		
X	F11-0043	JCO	12.02.22	appt	P	NZ		
sheet	revision	Y	B					
index	sheet	1	2					

dwg no

71991

A3

sheet 1 of 2

size


type

CUSTOMER

Drawing



VERT DR TMT

BtB RECEPT.



FCIconnect.com

Copyright FCI

mat'l. code SEE SHEET 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX																	
ltr	ecn no	dr	date	tolerances unless otherwise specified					title BtB RECEPT. VERT DR TMT																		
A	F04-0347	DLE	04.09.27	angles	linear	±0.3			scale 5:1																		
B	F06-0204	DLE	06.06.20																								
				±2'																							
				dr	D LEGRAND	04.09.27														dwg no				sheet 2 of 2			
				enr	P NIZZI	04.09.27			71991				A4														
				chr	D LE	04.09.27																					
				appd	P NZ	04.09.27																					
sheet index		revision sheet																									