


**TENMA®**

## REVISIONS

DOC. NO. SPC-F004 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			JAG	24-08-10	MRD	24-08-10	XXX	07-09-10

RoHS  
Compliant

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE: <b>DC Power Supply, Single Output, 56 Volts, 1.1 Amps</b>			
	JAG	24-08-10				
	CHECKED BY:	DATE:				
	MRD	24-08-10				
	APPROVED BY:	DATE:				
	XXX	07-09-10				
	SIZE		DWG. NO.		ELECTRONIC FILE	
A		XXX		01h9895		A
SCALE: NTS			U.O.M.: INCHES [mm]		SHEET: 1 OF 1	

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



## REVISIONS

DOC. NO. SPC-F004 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			JAG	24-08-10	MRD	24-08-10	XXX	07-09-10

**Features:**

- Single-Output 0 to 56 Volts, 0 to 1.1 Amps
- Coarse and Fine Voltage Controls
- Linear Regulation
- Constant Voltage or Constant Current Modes
- With Automatic Crossover and Mode Indication
- Separate, Digital Voltage and Current Meters

**Main Outputs**

Voltage Range: 0 to 56v maximum  
 Current Range: OA to 1.1A maximum  
 Operating Mode: Constant voltage or constant current with automatic Cross-over and indication.  
 Voltage Setting: By coarse and fine controls.  
 Current Setting: By single logarithmic control.  
 Load regulation: <0.01% of maximum O/P for a 90% load change.  
 Line regulation: 0.01% of maximum O/P for a 10% line voltage change.  
 Output impedance: Typically <5 milliohms. In constant voltage mode.  
 Typically >50kΩ in constant current mode.  
 Ripple & Moise (20MHz bandwidth): Typically <1mV rms, (CV mode).  
 Transient Response: <20µs to within 50 mV of set level for 90% load change.  
 Temp. Coefficient: Typically <100ppm/°C.  
 Output Protection: Outputs will withstand forward voltages of up to 20V above the rated output voltage. Reverse protection by diode clamp for currents up to 3A.  
 Status Indication: Output ON lamps. Constant current mode lamps.  
 Output Switch: Electronic. Preset voltage and current displayed when output is off.  
 Output Terminals: 4mm terminals on 19mm (0.75 inches) pitch.

**Meters (main outputs)**

Meter Types: Separate 3 digit meters for voltage and current with 14mm (0.56 inches) LED displays. Reading rate 4/sec.  
 Meter Accuracies: Voltage 0.3% ±1 digit. Current 0.6% ±1 digit.

Output Terminals  
 Standard Type: 4mm "binding post" terminals suitable for plugs or wires.

**Input Power**

AC Input: 230V or 115V ±10%, 50/60Hz. Adjustable internally. Installation Category II.  
 VA Rating: 160VA

**Temperature & Environmental**

Operating Range: +5°C to +40°C, 20% to 80% RH.  
 Storage Range: -40°C to 70°C.  
 Environmental: Indoor use at altitudes to 2000m, Pollution Degree 2.  
 Cooling: Silent fan-less convection cooling.  
 Safety: Complies with EN61010-1.  
 EMC: Complies with EN61326.

**Mechanical**

Size: 140 x 160 x 295 mm  
 Weight: 4.4kg

**Part Number Table**

Description	Part Number
DC Power Supply, Single Output, 56 Volts, 1.1 Amps	72-6907 CALIBRATED W/DATA

SPC-F004.DWG

TOLERANCES:  UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE: <b>DC Power Supply, Single Output, 56 Volts, 1.1 Amps</b>				
	JAG	24-08-10					
	CHECKED BY:	DATE:					
	MRD	24-08-10					
	APPROVED BY:	DATE:					
	XXX	07-09-10					
			SIZE	DWG. NO.	ELECTRONIC FILE		REV
			A	XXX	01h9895		A
			SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.