

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

FED. MFR. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING

9-11585

9-11585

DRAWING
NUMBERISSUE
17

REPLACES

RELEASE NO. PR-8532

CHECK

12JUN08

CMH

CHECK

8 MAR 80

C E B




CHECK

8 MAR 80

DRAWN

G J W

REVISIONS	DATE	BY	CHKD
A	1985 DWG	CO 46881	
B	28 JAN 80	G J W	
C	16 APR 90	G J W	
D	204537	G J W	
E	0007749	G J W	
F	0040541	G J W	
G	12JUN08	G J W	



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA		SCALE FULL
OPERATING FORCE - - - - - 28-54 OZ	CONTACT ARRANGEMENT	BREAK DISTANCE	DO NOT SCALE PRINT
DIFFERENTIAL TRAVEL - - - - .005 MAX	S P D T	.070 MIN	
RELEASE FORCE - - - - - 10 OZ MIN			
OVERTRAVEL - - - - - .188 MIN			
FULL OVERTRAVEL FORCE - - - 13 LB MAX			
			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.050 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
			WEIGHT

NOTE

1 - ALUMINUM ENCLOSURE FINISHED WITH PRIMER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[9-11585](#)