




## FINGERSTOCK GASKETS AND METAL GROUNDING PRODUCTS

As the world's leading fabricator of fingerstock, Laird Technologies has developed highly sophisticated, and often proprietary, shielding and grounding technology.

Our innovations are necessary to achieve outstanding combinations of performance parameters. From a vast selection of product configurations, platings and mounting techniques, to a full range of low compression force requirements and high transfer impedance characteristics, there is a Laird Technologies gasket or grounding product just right for the job.

Laird Technologies' Slot Mount Series of beryllium copper shielding gaskets is designed for use in a wide variety of slotted applications. This economical product line is ideal for both grounding and shielding applications.

## FEATURES

- Minimal slot fabrication cost
- Easy and cost-effective installation since fasteners and adhesives are not required
- Bi-directional wiping and compression action to accommodate a wide variety of designs
- The Slot Mount Series is available in your choice of finishes
- Ideal for grounding and shielding in the following electronic enclosure applications:
  - Front panel handles – Chassis covers
  - Plug-in units – Backplanes
  - Subrack assemblies
- Standard (77-Series) and UltraSoft® (78-Series low compression versions) are also supplied in 25.0 ft. (7.6 m) coils




global solutions: local support™

USA: +1.866.928.8181

Europe: +49.0.8031.2460.0

Asia: +86.755.2714.1166

## FINGERSTOCK DIMENSIONS





# Slot Mount Series Fingerstock Gaskets

Innovative **Technology**  
for a **Connected World**

## FINGERSTOCK DIMENSIONS

| SERIES | A                 | B                | C                | D                | E                | H                | M                | *N               | *O                | *P               | Q (R)            | LENGTH APPROX       | # OF FING |
|--------|-------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|-------------------|------------------|------------------|---------------------|-----------|
|        | RECOMMENDED       |                  |                  |                  |                  |                  |                  |                  |                   |                  |                  |                     |           |
| 77-010 | 0.320<br>(8.128)  | 0.110<br>(2.794) | 0.004<br>(0.102) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.260<br>(6.604)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 16.000<br>(406.400) | 86<br>—   |
|        | 0.600<br>(15.240) | 0.220<br>(5.588) | 0.005<br>(0.127) | 0.282<br>(7.163) | 0.032<br>(0.813) | 0.140<br>(3.556) | 0.180<br>(4.572) | 0.140<br>(3.556) | 0.520<br>(13.208) | 0.070<br>(1.778) | 0.040<br>(1.016) | 16.000<br>(406.400) | 57<br>—   |
| 77-015 | 0.600<br>(15.240) | 0.220<br>(5.588) | 0.005<br>(0.127) | N/A<br>—         | N/A<br>—         | 0.140<br>(3.556) | 0.180<br>(4.572) | 0.140<br>(3.556) | 0.520<br>(13.208) | 0.070<br>(1.778) | 0.040<br>(1.016) | 0.250<br>(6.350)    | 1<br>—    |
|        | 0.320<br>(8.128)  | 0.110<br>(2.794) | 0.004<br>(0.102) | N/A<br>—         | N/A<br>—         | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.260<br>(6.604)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.169<br>(4.293)    | 1<br>—    |
| 77-017 | 0.320<br>(8.128)  | 0.110<br>(2.794) | 0.004<br>(0.102) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.260<br>(6.604)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.356<br>(9.042)    | 2<br>—    |
|        | 0.320<br>(8.128)  | 0.110<br>(2.794) | 0.004<br>(0.102) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.260<br>(6.604)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.543<br>(13.792)   | 3<br>—    |
| 77-019 | 0.320<br>(8.128)  | 0.110<br>(2.794) | 0.004<br>(0.102) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.260<br>(6.604)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.730<br>(18.542)   | 4<br>—    |
|        | 0.600<br>(15.240) | 0.220<br>(5.588) | 0.005<br>(0.127) | 0.282<br>(7.163) | 0.032<br>(0.813) | 0.140<br>(3.556) | 0.180<br>(4.572) | 0.140<br>(3.556) | 0.520<br>(13.208) | 0.070<br>(1.778) | 0.040<br>(1.016) | 0.532<br>(13.513)   | 2<br>—    |
| 77-021 | 0.320<br>(8.128)  | 0.110<br>(2.794) | 0.004<br>(0.102) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.260<br>(6.604)  | 0.060<br>(1.524) | 0.035<br>(0.889) | 16.000<br>(406.400) | 86<br>—   |
|        | 0.370<br>(9.398)  | 0.130<br>(3.302) | 0.004<br>(0.102) | N/A<br>—         | N/A<br>—         | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.300<br>(7.620)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.225<br>(5.715)    | 1<br>—    |
| 77-024 | 0.370<br>(9.398)  | 0.130<br>(3.302) | 0.004<br>(0.102) | 0.250<br>(6.350) | 0.025<br>(0.635) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.300<br>(7.620)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.475<br>(12.065)   | 2<br>—    |
|        | 0.370<br>(9.398)  | 0.130<br>(3.302) | 0.004<br>(0.102) | 0.250<br>(6.350) | 0.025<br>(0.635) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.300<br>(7.620)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.725<br>(18.415)   | 3<br>—    |
| 77-025 | 0.370<br>(9.398)  | 0.130<br>(3.302) | 0.004<br>(0.102) | 0.250<br>(6.350) | 0.025<br>(0.635) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.300<br>(7.620)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 0.975<br>(24.765)   | 4<br>—    |
|        | 0.370<br>(9.398)  | 0.130<br>(3.302) | 0.005<br>(0.127) | 0.250<br>(6.350) | 0.025<br>(0.635) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.300<br>(7.620)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 1.225<br>(31.115)   | 5<br>—    |
| 77-028 | 0.370<br>(9.398)  | 0.130<br>(3.302) | 0.005<br>(0.127) | 0.250<br>(6.350) | 0.025<br>(0.635) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.300<br>(7.620)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 1.475<br>(37.465)   | 6<br>—    |
|        | 0.800<br>(20.320) | 0.320<br>(8.128) | 0.004<br>(0.102) | N/A<br>—         | N/A<br>—         | 0.200<br>(5.080) | 0.180<br>(4.572) | 0.220<br>(5.588) | 0.720<br>(18.288) | 0.070<br>(1.778) | 0.040<br>(1.016) | 0.343<br>(8.712)    | 1<br>—    |
| 77-030 | 0.800<br>(20.320) | 0.320<br>(8.128) | 0.004<br>(0.102) | 0.375<br>(9.525) | 0.032<br>(0.813) | 0.200<br>(5.080) | 0.180<br>(4.572) | 0.220<br>(5.588) | 0.720<br>(18.288) | 0.070<br>(1.778) | 0.040<br>(1.016) | 0.718<br>(18.237)   | 2<br>—    |
|        | 0.800<br>(20.320) | 0.320<br>(8.128) | 0.005<br>(0.127) | 0.375<br>(9.525) | 0.032<br>(0.813) | 0.200<br>(5.080) | 0.180<br>(4.572) | 0.220<br>(5.588) | 0.720<br>(18.288) | 0.070<br>(1.778) | 0.040<br>(1.016) | 1.093<br>(27.762)   | 3<br>—    |
| 77-032 | 0.800<br>(20.320) | 0.320<br>(8.128) | 0.005<br>(0.127) | 0.375<br>(9.525) | 0.032<br>(0.813) | 0.200<br>(5.080) | 0.180<br>(4.572) | 0.220<br>(5.588) | 0.720<br>(18.288) | 0.070<br>(1.778) | 0.040<br>(1.016) | 1.468<br>(37.287)   | 4<br>—    |
|        | 0.310<br>(7.874)  | 0.120<br>(3.048) | 0.003<br>(0.076) | 0.250<br>(6.350) | 0.020<br>(0.508) | 0.090<br>(2.286) | 0.115<br>(2.921) | 0.095<br>(2.413) | 0.250<br>(6.350)  | 0.040<br>(1.016) | 0.015<br>(0.381) | 0.480<br>(12.192)   | 2<br>—    |
| 77-036 | 0.310<br>(7.874)  | 0.120<br>(3.048) | 0.003<br>(0.076) | 0.250<br>(6.350) | 0.020<br>(0.508) | 0.090<br>(2.286) | 0.115<br>(2.921) | 0.095<br>(2.413) | 0.250<br>(6.350)  | 0.040<br>(1.016) | 0.015<br>(0.381) | 0.980<br>(24.892)   | 4<br>—    |
|        | 0.310<br>(7.874)  | 0.120<br>(3.048) | 0.003<br>(0.076) | 0.250<br>(6.350) | 0.020<br>(0.508) | 0.090<br>(2.286) | 0.115<br>(2.921) | 0.095<br>(2.413) | 0.250<br>(6.350)  | 0.040<br>(1.016) | 0.015<br>(0.381) | 1.480<br>(37.592)   | 6<br>—    |
| 77-038 | 0.310<br>(7.874)  | 0.120<br>(3.048) | 0.003<br>(0.076) | 0.250<br>(6.350) | 0.020<br>(0.508) | 0.090<br>(2.286) | 0.115<br>(2.921) | 0.095<br>(2.413) | 0.250<br>(6.350)  | 0.040<br>(1.016) | 0.015<br>(0.381) | 1.980<br>(50.292)   | 8<br>—    |
|        | 0.280<br>(7.112)  | 0.110<br>(2.794) | 0.002<br>(0.051) | N/A<br>—         | N/A<br>—         | 0.075<br>(1.905) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.220<br>(5.588)  | 0.040<br>(1.016) | 0.030<br>(0.762) | 0.169<br>(4.293)    | 1<br>—    |
| 77-040 | 0.280<br>(7.112)  | 0.110<br>(2.794) | 0.002<br>(0.051) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.075<br>(1.905) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.220<br>(5.588)  | 0.040<br>(1.016) | 0.030<br>(0.762) | 0.356<br>(9.042)    | 2<br>—    |
|        | 0.280<br>(7.112)  | 0.110<br>(2.794) | 0.002<br>(0.051) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.075<br>(1.905) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.220<br>(5.588)  | 0.040<br>(1.016) | 0.030<br>(0.762) | 0.543<br>(13.792)   | 3<br>—    |
| 77-042 | 0.280<br>(7.112)  | 0.110<br>(2.794) | 0.002<br>(0.051) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.075<br>(1.905) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.220<br>(5.588)  | 0.040<br>(1.016) | 0.030<br>(0.762) | 0.730<br>(18.542)   | 4<br>—    |
|        | 0.320<br>(8.128)  | 0.110<br>(2.794) | 0.004<br>(0.102) | 0.187<br>(4.750) | 0.018<br>(0.457) | 0.085<br>(2.159) | 0.110<br>(2.794) | 0.090<br>(2.286) | 0.260<br>(6.604)  | 0.040<br>(1.016) | 0.020<br>(0.508) | 1.104<br>(28.042)   | 6<br>—    |

\* May vary depending upon application.

| SERIES | A        | B       | C       | D       | E       | H       | M       | *N          | *O       | *P      | Q (R)   | LENGTH APPROX | # OF FING |
|--------|----------|---------|---------|---------|---------|---------|---------|-------------|----------|---------|---------|---------------|-----------|
|        |          |         |         |         |         |         |         | RECOMMENDED |          |         |         |               |           |
| 77-045 | 0.320    | 0.110   | 0.004   | N/A     | N/A     | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 0.169         | 1         |
|        | (8.128)  | (2.794) | (0.102) | —       | —       | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (4.293)       | —         |
| 77-046 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 0.356         | 2         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (9.042)       | —         |
| 77-047 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 0.543         | 3         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6604)   | (1.524) | (1.016) | (13.792)      | —         |
| 77-048 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 0.730         | 4         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (18.542)      | —         |
| 77-050 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 0.917         | 5         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (23.292)      | —         |
| 77-051 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 1.104         | 6         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (28.042)      | —         |
| 77-052 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 1.291         | 7         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (32.791)      | —         |
| 77-053 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 1.478         | 8         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (37.541)      | —         |
| 77-054 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 1.665         | 9         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (42.291)      | —         |
| 77-055 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.060   | 0.040   | 1.852         | 10        |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.524) | (1.016) | (47.041)      | —         |
| 77-058 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.040   | 0.020   | 0.917         | 5         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.016) | (0.508) | (23.292)      | —         |
| 77-059 | 0.370    | 0.130   | 0.004   | 0.250   | 0.025   | 0.085   | 0.110   | 0.090       | 0.310    | 0.040   | 0.020   | 16.000        | 64        |
|        | (9.398)  | (3.302) | (0.102) | (6.350) | (0.635) | (2.159) | (2.794) | (2.286)     | (7.874)  | (1.016) | (0.508) | (406.400)     | —         |
| 77-062 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.048   | 0.025   | 0.169         | 1         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.219) | (0.635) | (4.293)       | —         |
| 77-063 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.048   | 0.025   | 0.356         | 2         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.219) | (0.635) | (9.042)       | —         |
| 77-064 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.048   | 0.025   | 0.543         | 3         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.219) | (0.635) | (13.792)      | —         |
| 77-065 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.048   | 0.025   | 0.730         | 4         |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.219) | (0.635) | (18.542)      | —         |
| 77-070 | 0.320    | 0.110   | 0.004   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.062   | 0.035   | 16.000        | 86        |
|        | (8.128)  | (2.794) | (0.102) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.575) | (0.889) | (406.400)     | —         |
| 77-076 | 0.600    | 0.220   | 0.005   | N/A     | N/A     | 0.140   | 0.180   | 0.140       | 0.520    | 0.070   | 0.020   | 0.340         | 1         |
|        | (15.240) | (5.588) | (0.127) | —       | —       | (3.556) | (4.572) | (3.556)     | (13.208) | (1.778) | (0.508) | (8.636)       | —         |
| 77-087 | 0.563    | 0.110   | 0.003   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.040   | 0.020   | 1.291         | 7         |
|        | (14.300) | (2.794) | (0.076) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.016) | (0.508) | (32.791)      | —         |
| 77-088 | 0.563    | 0.110   | 0.003   | 0.187   | 0.018   | 0.085   | 0.110   | 0.090       | 0.260    | 0.040   | 0.020   | 1.478         | 8         |
|        | (14.300) | (2.794) | (0.076) | (4.750) | (0.457) | (2.159) | (2.794) | (2.286)     | (6.604)  | (1.016) | (0.508) | (37.541)      | —         |
| 77-089 | 0.600    | 0.220   | 0.005   | 0.282   | 0.032   | 0.140   | 0.180   | 0.140       | 0.520    | 0.070   | 0.040   | 0.810         | 3         |
|        | (15.240) | (5.588) | (0.127) | (7.163) | (0.813) | (3.556) | (4.572) | (3.556)     | (13.208) | (1.778) | (1.016) | (20.574)      | —         |
| 77-094 | 0.358    | 0.128   | 0.003   | 0.202   | 0.018   | 0.110   | 0.100   | 0.115       | 0.300    | 0.030   | 0.030   | 0.389         | 2         |
|        | (9.093)  | (3.251) | (0.076) | (5.131) | (0.457) | (2.794) | (2.54)  | (2.921)     | (7.620)  | (0.762) | (0.762) | (9.881)       | —         |
| 77-096 | 0.600    | 0.220   | 0.005   | 0.282   | 0.032   | 0.140   | 0.180   | 0.095       | 0.520    | 0.040   | 0.040   | 1.096         | 4         |
|        | (15.240) | (5.588) | (0.127) | (7.163) | (0.813) | (3.556) | (4.572) | (2.413)     | (13.208) | (1.016) | (1.016) | (27.838)      | —         |
| 77-097 | 0.600    | 0.220   | 0.005   | 0.375   | 0.032   | 0.140   | 0.180   | 0.140       | 0.520    | 0.070   | 0.040   | 16.000        | 43        |
|        | (15.240) | (5.588) | (0.127) | (9.525) | (0.813) | (3.556) | (4.572) | (3.556)     | (13.208) | (1.778) | (1.016) | (406.400)     | —         |
| 77-099 | 0.600    | 0.220   | 0.005   | 0.375   | 0.032   | 0.140   | 0.180   | 0.140       | 0.520    | 0.070   | 0.040   | 1.378         | 5         |
|        | (15.240) | (5.588) | (0.127) | (9.525) | (0.813) | (3.556) | (4.572) | (3.556)     | (13.208) | (1.778) | (1.016) | (35.001)      | —         |
| 77-100 | 0.600    | 0.220   | 0.005   | 0.375   | 0.032   | 0.140   | 0.180   | 0.140       | 0.520    | 0.070   | 0.040   | 1.660         | 6         |
|        | (15.240) | (5.588) | (0.127) | (9.525) | (0.813) | (3.556) | (4.572) | (3.556)     | (13.208) | (1.778) | (1.016) | (42.164)      | —         |
| 77-101 | 0.600    | 0.220   | 0.005   | 0.375   | 0.032   | 0.140   | 0.180   | 0.140       | 0.520    | 0.070   | 0.040   | 1.942         | 7         |
|        | (15.240) | (5.588) | (0.127) | (9.525) | (0.813) | (3.556) | (4.572) | (3.556)     | (13.208) | (1.778) | (1.016) | (49.327)      | —         |