




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		B	REV PER ECO-14-014238	20SEP2014	AP	RP




RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE SHOWN
SCALE 4:1

- REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- MATERIAL:
CONTACT & SHIELD - PHOSPHOR BRONZE
HOUSING & CHICKLET - GLASS FILLED POLYESTER
- FINISH: SIGNAL AND GROUND CONTACTS:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
COMPLIANT PIN AREA: 0.5 µm MIN MATTE TIN OVER BASE PLATING
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN
- DIMENSION APPLIES TO CENTERLINE OF THRU HOLE
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



TOP SURFACE OF DAUGHTER CARD



6469169-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. J. MAGARO 18 JUL 2004	 TE Connectivity		
DIMENSIONS:		CHK R. A. PATTERSON 18 JUL 2004			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. PATTERSON 31 MAR 2006	NAME	HEADER ASSEMBLY, RIGHT ANGLE, 2 PAIR, COPLANAR, HMZd	
	0 PLC ±.2	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
	1 PLC ±0.2	APPLICATION SPEC			
	2 PLC ±0.13	WEIGHT	A1	00779	C=6469169
	3 PLC ±0.05	CUSTOMER DRAWING			
	4 PLC ±.1	SCALE	6:1	SHEET	1 OF 1
	ANGLES ±.1°	REV	B		
	FINISH				