

Absorbent Specification Guide

www.BradyID.com/SPC

Part Numbers	Type	Size	Perforated	Absorbency Factor (gl/gs)	Absorbency Capacity (gal)	Shipping Wt. (lbs)	Pallet Qty.*	Quantity
SC-Cart	Spill Control Cart	36 x 18 x 38-3/8	n/a	n/a	n/a	180	1	1/each
SC-D15	15" Dowel Rod	15"	n/a	n/a	n/a	n/a	n/a	1 rod
SC-D40	40" Dowel Rod	40"	n/a	n/a	n/a	n/a	n/a	1 rod
SC-DK	Sump Drain Kit	n/a	n/a	n/a	n/a	2	100	1/case
SC-MB	Wall Mount	n/a	n/a	n/a	n/a	n/a	n/a	1 each
SC-DP2	2-Drum Spill Pallet	26"W X 52"L X 17"H	n/a	68.7	2,500	46.5	10	1/each
SC-DP4	4-Drum Spill Pallet	52"W X 52"L X 17"H	n/a	128.9	5,000	89	10	1/each
SC-DPR	Spill Pallet Ramp	32.5"W X 70"L	n/a	n/a	650	47.5	3	1/each
SC-SD2	2 Drum Spill Deck	26"W X 52"L X 6"H	n/a	21.2	2,500	31	15	1/each
SIR36	Heavy Wt. Rug	36"x300'	No	8.5	59	50	12	1/bale
SIR72	Heavy Wt. Rug	72"x150'	No	8.5	59	50	12	1/bale
SIR36150	Heavy Wt. Rug	36"x150'	No	12.5	45	25	24	1/bale
SKA-20	Universal	21"Dia. X 18"H	n/a	n/a	15	27	18	1/each
SKA-20-RESCUE	Universal	21"Dia. X 18"H	n/a	n/a	15	20	18	1/each
SKA20-TAA	Universal	21"Dia. X 18"H	n/a	n/a	15	26	18	1/each
SKA30	Universal	21.125"Dia. X 28.5"H	n/a	n/a	36	41	18	1/each
SKA30-TAA	Universal	21.125"Dia. X 28.5"H	n/a	n/a	36	41	18	1/each
SKA-55	Universal	24"Dia. X 37"H	n/a	n/a	38	57	8	1/each
SKA55-TAA	Universal	24"Dia. X 37"H	n/a	n/a	38	56	8	1/each
SKA-55W	Universal*	24"Dia. X 37"H	n/a	n/a	38	57	8	1/each
SKA65	Universal	31"Dia. X 33.5"H	n/a	n/a	63	100	3	1/each
SKA65-TAA	Universal	31"Dia. X 33.5"H	n/a	n/a	63	100	3	1/each
SKA-65W	Universal	31"Dia. X 33.5"H	n/a	n/a	63	100	3	1/each
SKA-95	Universal	31.5"Dia. X 35"H	n/a	n/a	75	107	3	1/each
SKA-95W	Universal*	31.5"Dia. X 35"H	n/a	n/a	75	107	3	1/each
SKA-ATK	Universal	20"L X 16"W X 4"H	n/a	n/a	7	36.5	24	4/case
SKA-ATK-TAA	Universal	20"L X 16"W X 4"H	n/a	n/a	7	36.5	24	4/case
SKA-BKT	Universal	14"Dia. X 18"H	n/a	n/a	9	9	60	1/each
SKA-BKTACID	Acid Neutralizing Spill Kit	13.5" Dia. x 18"H	n/a	n/a	4.5	16.5	60	1/each
SKA-BKTBASE	Base Neutralizer Spill Kit	13.5" Dia. x 18"H	n/a	n/a	4.5	16.5	60	1/each
SKA-BKT-TAA	Universal	14"Dia. X 18"H	n/a	n/a	6	9	60	1/each
SKA-CFB	Universal	25.5"L x 17"W x 21.5"H	n/a	n/a	15	25	20	1 each
SKA-CFB-TAA	Universal	25.5"L x 17"W x 21.5"H	n/a	n/a	15	25	20	1 each
SKA-K2	Universal	18"L X 17"W X 39"H	n/a	n/a	22	42	10	1/each
SKA-LT	Universal	47"L X 34"W X 43"H	n/a	n/a	126	164	1	1/each
SKA-PP	Universal	20"L X 16"W X 4"H	n/a	n/a	5	24	20	1/each
SKA-PP-TAA	Universal	20"L X 16"W X 4"H	n/a	n/a	5	24	20	1/each
SKA-SAK	Universal	32"L X 20"W X 12"H	n/a	n/a	10.75	10	20	1/each
SKA-SRP	Universal	9.75"D X 10.5"H	n/a	n/a	4.5	2.5	90	1/each
SKA-XLT	Universal	57.5"L X 40.5"W X 47"H	n/a	n/a	174	221	1	1/each
SK-CAMO	Camouflaged Vehicle Spill Kit	n/a	n/a	n/a	11.5	9	50	1/each
SK-CAMO-RS	Camouflaged Vehicle Spill Kit with RuptureSEAL	n/a	n/a	n/a	11.5	9	50	1/each
SKH-20	Chemical	21"Dia. X 18"H	n/a	n/a	15	26	18	1/each
SKH-20-RESCUE	Chemical	21"Dia. X 18"H	n/a	n/a	15	20	18	1/each
SKH30	Chemical	21.125"Dia. X 28.5"H	n/a	n/a	36	41	18	1/each
SKH-55	Chemical	24"Dia. X 37"H	n/a	n/a	38	52	8	1/each
SKH-55W	Chemical*	24"Dia. X 37"H	n/a	n/a	38	52	8	1/each
SKH65	Chemical	31"Dia. X 33.5"H	n/a	n/a	63	100	3	1/each
SKH-65W	Chemical	31"Dia. X 33.5"H	n/a	n/a	63	100	3	1/each
SKH-95	Chemical	31.5"Dia. X 35"H	n/a	n/a	75	104	3	1/each
SKH-95W	Chemical*	31.5"Dia. X 35"H	n/a	n/a	75	104	3	1/each
SKH-ATK	Chemical	20"L X 16"W X 4"H	n/a	n/a	7	25	24	4/case
SKH-BKT	Chemical	14"Dia. X 18"H	n/a	n/a	9	8	60	1/each
SKH-CFB	Chemical	25.5"L x 17"W x 21.5"H	n/a	n/a	15	25	20	1 each
SKH-K2	Chemical	18"L X 17"W X 39"H	n/a	n/a	22	42	10	1/each

* In an effort to reduce shipping costs for our customers, pallet quantities may vary.

DISCLAIMER: The above properties are "nominal" values used for PROCESS CONTROL when the product is produced and/or inspected. Performance "nominals" may vary depending upon the specific application, and/or the environment being applied, stored, or shipped. The "Absorbency" Spec and "SPCTM004" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.