




RECOMMENDED PCB LAYOUT



- NOTES:
1. INSULATOR MATERIAL: NYLON 6T.
 2. CONTACT MATERIAL: BRASS.
 3. PLATING: GOLD FLASH OVERALL.
 4. OPERATING TEMPERATURE: -40°C ~ 105°C.
 5. PROCESSING TEMP: 230°C FOR 60 SECONDS MAX.
(260°C, 10 SEC.)
 6. UL FLAMMABILITY RATING: 94V-0.
 7. VOLTAGE RATING: 20m OHMS MAX.
 8. CURRENT RATING: 3 AMP PER CONTACT.
 9. VOLTAGE DROP: AC 500 V.
 10. INSULATION RESISTANCE: 1000 MEGA OHMS.

REVISIONS				
REV.	ECO. NO	DESCRIPTION	DATE	BY
A	1682	INITIAL RELEASE	5/12/2008	VJ
B	1682	UPDATE DIM 'C', TABLE, NOTE 3 & TOLERANCE BLOCK	11/12/2008	JH


PART NUMBER CODING

SBH11 - NBPC - D _ _ - SM - _ _

NUMBER OF POSITIONS
(CONTACTS PER ROW)

TERMINATION
SURFACE MOUNT

COLOR
BK = BLACK
YE = YELLOW
RE = RED
BL = BLUE
GR = GREEN
GY = GREY
WH = WHITE
OR = ORANGE



PART NUMBER	POSITIONS/ CONTACTS	A		B		C	
		INCH	MM	INCH	MM	INCH	MM
SBH11-NBPC-D03-SM- _ _	03/06	0.200	5.08	0.595	15.12	0.505	12.82
SBH11-NBPC-D04-SM- _ _	04/08	0.300	7.62	0.695	17.66	0.605	15.36
SBH11-NBPC-D05-SM- _ _	05/10	0.400	10.16	0.795	20.20	0.705	17.90
SBH11-NBPC-D06-SM- _ _	06/12	0.500	12.70	0.895	22.74	0.805	20.44
SBH11-NBPC-D07-SM- _ _	07/14	0.600	15.24	0.995	25.28	0.905	22.98
SBH11-NBPC-D08-SM- _ _	08/16	0.700	17.78	1.095	27.82	1.005	25.52
SBH11-NBPC-D10-SM- _ _	10/20	0.900	22.86	1.295	32.90	1.205	30.60
SBH11-NBPC-D12-SM- _ _	12/24	1.100	27.94	1.495	37.98	1.405	35.68
SBH11-NBPC-D13-SM- _ _	13/26	1.200	30.48	1.595	40.52	1.505	38.22
SBH11-NBPC-D15-SM- _ _	15/30	1.400	35.56	1.795	45.60	1.705	43.30
SBH11-NBPC-D17-SM- _ _	17/34	1.600	40.64	1.995	50.68	1.905	48.38
SBH11-NBPC-D20-SM- _ _	20/40	1.900	48.26	2.295	58.30	2.205	56.00
SBH11-NBPC-D22-SM- _ _	22/44	2.100	53.34	2.495	63.38	2.405	61.08
SBH11-NBPC-D25-SM- _ _	25/50	2.400	60.96	2.795	71.00	2.705	68.70
SBH11-NBPC-D30-SM- _ _	30/60	2.900	73.66	3.295	83.70	3.205	81.40
SBH11-NBPC-D32-SM- _ _	32/64	3.100	78.74	3.495	88.78	3.405	86.48



RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES[MM]
TOLERANCES:
ANGULAR: ± 1°
.XX = ±.012 [0.30]
.XXX = ±.008 [0.20]
.XXXX = ±.004 [0.10]
PARENTHEetical INFORMATION IS FOR
REFERENCE ONLY
INTERPRET DIMENSIONS AND GEOMETRIC
TOLERANCING
PER: ANSI Y14.5-1984

DATE	NAME
5/12/2008	V. JARA
THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.	

DESCRIPTION: BOX HEADER, .100[2.54] CC/RS	
PART NUMBER SBH11-NBPC-D _ _ -SM- _ _	
SIZE C	DWG. NO. 11093
SCALE: NONE	REV B
SHEET 1 OF 1	