

# □ MN102H57K

Type	MN102H57K		
ROM (x16-bit)	256 K		
RAM (x16-bit)	8 K		
Package	QFP084-P-1818E *Pb free		
Minimum Instruction Execution Time	83 ns (at 3.6 V to 3.0 V, 12 MHz)		
Interrupts	External (6 lines) Internal (30 lines) : Timer × 11, A/D × 1, Undefined command × 1, RESET × 1, OSD × 2, Serial × 4, I <sup>2</sup> C × 1, Caption × 4, Remote control × 1, Address coincidence × 4		
Timer Counter	8-bit timer × 4 16-bit timer × 2 Watchdog timer: 17-bit × 1		
Serial Interface	I <sup>2</sup> C × 1: for multimaster mode, bus line (output) has 2 systems Sync serial / I <sup>2</sup> C (master) / UART × 2		
Caption	• Built-in sync separator × 2		
I/O Pins	I/O	66	• Common use
A/D Inputs	8-bit × 12-ch. (with S/H)		
D/A Inputs	4-bit × 4-ch. (analog R, G, B, YM output)		
PWM	8-bit × 7-ch.		
Special Ports	Remote control reception		
CRTC	3-layer display (graphics, characters, splits)		
Notes	Remote control input discriminant circuit built-in		


## Electrical Characteristics

### D/A characteristics

Parameter	Symbol	Condition	Limit			Unit
			min	typ	max	
D/A full-scale output current	IFS	RL = 200 Ω, VREF = 1.2 V, RIREF = 1.2 kΩ	4.5	5.0	5.5	mA
D/A output voltage setting range	VO	RL = 200 Ω, VREF = 1.2 V, RIREF = 1.2 kΩ	0.9		1.1	V
D/A non-linear error	NLE	RL = 200 Ω, VREF = 1.2 V, RIREF = 1.2 kΩ			±0.5	LSB
D/A differential non-linear error	DNLE	RL = 200 Ω, VREF = 1.2 V, RIREF = 1.2 kΩ			±0.5	LSB
D/A channel interval error	IFS	VREF = 1.2 V, RIREF = 1.2 kΩ, Error from 4-channel average IFS			±5	%

(Ta = 25°C, VDD = AVDD = 3.3 V, VSS = 0 V, fosc = 4 MHz)

## Pin Assignment



QFP084-P-1818E \*Pb free

\*1: 5 V dielectric Nch open drain output pin

\*2: MN102H57K (VDD), MN102HF57K (VPP)

## Support Tool

<b>In-circuit Emulator</b>	PX-ICE102H57-QFP084-P-1818E	
<b>Flash Memory Built-in Type</b>	Type	MN102HF57K
	ROM (x 16-bit)	256 K
	RAM (x 16-bit)	8 K
	Minimum instruction execution time	83 ns (at 3.6 V to 3.0 V, 12 MHz)
	Package	QFP084-P-1818E *Pb free

**Request for your special attention and precautions in using the technical information and semiconductors described in this material**

- (1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technologies described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.
- (2) The technical information described in this material is limited to showing representative characteristics and applied circuit examples of the products. It does not constitute the warranting of industrial property, the granting of relative rights, or the granting of any license.
- (3) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).  
Consult our sales staff in advance for information on the following applications:
  - Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
  - Any applications other than the standard applications intended.
- (4) The products and product specifications described in this material are subject to change without notice for reasons of modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.  
Even when the products are used within the guaranteed values, redundant design is recommended, so that such equipment may not violate relevant laws or regulations because of the function of our products.
- (6) When using products for which dry packing is required, observe the conditions (including shelf life and after-unpacking standby time) agreed upon when specification sheets are individually exchanged.
- (7) No part of this material may be reprinted or reproduced by any means without written permission from our company.

**Please read the following notes before using the datasheets**

- A. These materials are intended as a reference to assist customers with the selection of Panasonic semiconductor products best suited to their applications.  
Due to modification or other reasons, any information contained in this material, such as available product types, technical data, and so on, is subject to change without notice.  
Customers are advised to contact our semiconductor sales office and obtain the latest information before starting precise technical research and/or purchasing activities.
- B. Panasonic is endeavoring to continually improve the quality and reliability of these materials but there is always the possibility that further rectifications will be required in the future. Therefore, Panasonic will not assume any liability for any damages arising from any errors etc. that may appear in this material.
- C. These materials are solely intended for a customer's individual use.  
Therefore, without the prior written approval of Panasonic, any other use such as reproducing, selling, or distributing this material to a third party, via the Internet or in any other way, is prohibited.