

RoHS **313/315 Series** Lead-Free 3AG, Slo-Blo® Fuse



Description

The 3AG Slo-Blo® fuse solves a broad range of application requirements while offering reliable performance and cost-effective circuit protection.

The fuse catalog number with the suffix “ID” instantly identifies itself upon opening by showing a discoloration of its glass body. Guesswork and time consuming circuit testing are eliminated. This unique design offers the same quality performance characteristics as the standard 3AG Slo-Blo® Fuse design.

Agency Approvals

Agency	Agency File Number	Ampere Range
	E10480	10mA - 10A**
	LR 29862	10mA - 10A**/15A**
	E10480	10A - 30A
	NBK 040205- E10480B/D/F/G/H	1A - 10A**/ 15A**
	SU05001- 5007/5008/5009/6004	2.25A - 8A
		10mA - 10A**/15A**

Features

- In accordance with UL Standard 248-14
- Available in cartridge and axial lead format and with various forming dimensions
- RoHS compliant and Lead-free

Applications

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

Electrical Characteristics by Series

% of Ampere Rating	Ampere Rating	Opening Time
100%	10mA – 30A	4 hours, Minimum
135%	10mA – 30A	1 hour, Maximum
200%	10mA – 15A	5 sec., Min., 30 sec., Max
	20A – 30A	5 sec., Min., 60 sec Max


Electrical Characteristic Specifications by Item

Amp Code	Ampere Rating (A)	Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Agency Approvals					
						UL	SP	Q	RU	PS E	CE
.010	0.01	250	35A@250Vac 10KA@125Vac	4300.0000	0.000121	x	x				x
.031	0.031	250		430.0000	0.00303	x	x				x
.040	0.04	250		300.0000	0.00630	x	x				x
.062	0.062	250		120.0000	0.0210	x	x				x
.100	0.1	250		43.0000	0.0850	x	x				x
.125	0.125	250		30.0000	0.152	x	x				x
.150	0.15	250		20.0000	0.270	x	x				x
.175	0.175	250		8.6700	0.177	x	x				x
.187	0.187	250		8.0100	0.230	x	x				x
.200	0.2	250		6.5900	0.270	x	x				x
.250	0.25	250		4.2700	0.385	x	x				x
.300	0.3	250		3.1350	0.730	x	x				x
.375	0.375	250		2.0950	1.23	x	x				x
.400	0.4	250		1.8750	1.35	x	x				x
.500*	0.5	250		1.2600	2.55	x	x				x
.600	0.6	250		0.9120	4.00	x	x				x
.700	0.7	250		0.7000	5.90	x	x				x
.750	0.75	250		0.6215	7.16	x	x				x
.800	0.8	250		0.5540	8.00	x	x				x
001.*	1	250		0.3750	14.0	x	x			x	x
01.2	1.2	250	100A@250Vac 10KA@125Vac	0.2780	21.5	x	x			x	x
1.25	1.25	250		0.2600	24.0	x	x			x	x
01.5*	1.5	250		0.1910	38.0	x	x			x	x
01.6	1.6	250		0.1710	49.6	x	x			x	x
01.8	1.8	250		0.1410	58.0	x	x			x	x
002.*	2	250		0.1169	77.0	x	x			x	x
2.25	2.25	250		0.0968	121	x	x	x		x	x
02.5	2.5	250		0.0811	130	x	x	x		x	x
02.8	2.8	250		0.0675	170	x	x	x		x	x
003.*	3	250		0.0593	200	x	x	x		x	x
03.2	3.2	250		0.0529	209	x	x	x		x	x
004.*	4	250	200A@250Vac 10KA@125Vac	0.0311	76.1	x	x	x		x	x
005.*	5	250		0.0214	140	x	x	x		x	x
6.25*	6.25	250		0.0154	242	x	x	x		x	x
06.3	6.3	250		0.0154	242	x	x	x		x	x
007.*	7	250		0.0128	347	x	x	x		x	x
008.*	8	250	300A@32Vac	0.0111	445	x	x	x		x	x
010.*+	10	250		0.0083	760	x	x			x	x
010.*	10	32		0.0083	760				x		
012.	12	32		0.0065	1200				x		
015.**	15	125		0.0050	1870		x		x	x	x
015.	15	32		0.0050	1870				x		
020.	20	32		0.0022	9560				x		
025.	25	32		0.0017	16500				x		
030.	30	32		0.0012	26900				x		

* For 313series, these ratings available with an indicating option. Add the "ID" designation to the series number. i.e. 313.500ID.

** These 2 ratings are designed for special voltage requirement. For 10A, it is available as 250Vac rated and the part number is 0313010. MX250P; for 15A, it is available as 125Vac rated and the part number is 0315015.MX125P.


Temperature Derating Curve




A - For 313/315 Series, from 10mA to 150mA

B - For all other ampere ratings of 313/315 series

Average Time Current Curves



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation
Preheat:	
(Depends on Flux Activation Temperature)	(Typical Industry Recommendation)
Temperature Minimum:	100° C
Temperature Maximum:	150° C
Preheat Time:	60-180 seconds
Solder Pot Temperature:	260° C Maximum
Solder Dwell Time:	2-5 seconds

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350° C +/- 5°C
Heating Time: 5 seconds max.


Note: These devices are not recommended for IR or Convection Reflow process.

Product Characteristics


Materials	Body: Glass Cap: Nickel-plated brass Leads: Tin-plated Copper
Terminal Strength	MIL-STD-202G, Method 211A, Test Condition A
Solderability	Reference IEC 60127 Second Edition 2003-01 Annex A
Product Marking	Cap1: Brand logo, current and voltage ratings Cap2: Series and agency approval marks

Operating Temperature	-55°C to +125°C
Thermal Shock	MIL-STD-202G, Method 107G, Test Condition B: (5 cycles -65°C to +125°C)
Vibration	MIL-STD-202G, Method 201 A
Humidity	MIL-STD-202G, Method 103B, Test Condition A: High RH (95%) and Elevated temperature (40°C) for 240 hours
Salt Spray	MIL-STD-202G, Method 101D, Test Condition B

Dimensions



Part Numbering System



Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Reel Size
313 Series				
Bulk	N/A	5	VX	N/A
Bulk	N/A	100	HX	N/A
Bulk	N/A	100	HXID	N/A
Bulk	N/A	1000	MX	N/A
Bulk	N/A	1000	MX250	N/A
Bulk	N/A	100	HXCCD	N/A
Bulk	N/A	100	VXID	N/A
315 Series				
Bulk	N/A	5	VX	N/A
Bulk	N/A	100	HX	N/A
Bulk	N/A	1000	MX	N/A
Bulk	N/A	1000	MX125	N/A
Bulk	N/A	1000	MXB	N/A
Bulk	N/A	100	HXB	N/A
Bulk	N/A	1000	MXBB	N/A
Bulk	N/A	1000	MXSL	N/A
Bulk	N/A	1000	MXB	N/A
Bulk	N/A	1000	MXSL	N/A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[0315020.MXBP](#) [031506.3MXP](#) [0315010.MXP](#) [0315008.MXP](#) [031501.8HXP](#) [031501.2HXP](#) [0315003.MXP](#)
[0315.100MXP](#) [0315.031HXP](#) [03152.25MXP](#) [031501.5HXP](#) [031502.8HXP](#) [0315.200MXP](#) [031502.5MXP](#)
[0315.800HXP](#) [0315012.MXP](#) [03156.25MXP](#) [0315010.HXP](#) [0315.150MXP](#) [0315015.HXP](#) [0315.250MXP](#)
[0315.150HXP](#) [0315003.HXP](#) [0315.300MXP](#) [0315.700MXP](#) [0315.500MXP](#) [0315020.HXP](#) [031503.2HXP](#)
[03152.25HXP](#) [0315030.HXP](#) [031501.2MXP](#) [031501.6HXP](#) [0315001.MXP](#) [0315.062HXP](#) [0315.700HXP](#)
[0315007.HXP](#) [0315.010MXP](#) [031503.2MXP](#) [031502.5HXP](#) [0315.375MXP](#) [0315004.MXP](#) [0315.600MXP](#)
[0315.040HXP](#) [0315004.HXP](#) [0315.040MXP](#) [03151.25MXP](#) [0315.375HXP](#) [03156.25HXP](#) [0315002.MXP](#)
[0315.600HXP](#) [0315.175MXP](#) [0315020.MXP](#) [0315.500HXP](#) [0315008.HXP](#) [0315.125HXP](#) [0315007.MXP](#)
[03151.25HXP](#) [0315.800MXP](#) [0315.750MXP](#) [0315005.HXP](#) [0315.400MXP](#) [0315.300HXP](#) [031501.8MXP](#)
[0315030.MXP](#) [0315.010HXP](#) [0315.175HXP](#) [0315.250HXP](#) [0315002.HXP](#) [0315015.MXP](#) [0315.750HXP](#)
[0315.062MXP](#) [0315012.HXP](#) [0315.100HXP](#) [0315.187MXP](#) [0315005.MXP](#) [0315025.MXP](#) [0315.031MXP](#)
[031502.8MXP](#) [031501.6MXP](#) [0315.200HXP](#) [031501.5MXP](#) [0315.187HXP](#) [031506.3HXP](#) [0315.400HXP](#)
[0315.125MXP](#) [0315001.HXP](#) [0315025.HXP](#) [0315005.MXBP](#) [0315015.MXBP](#) [0315025.MXBP](#) [0315003.MXBP](#)
[0315.125MXBP](#) [03152.25MXBP](#) [0315007.HXBP](#) [0315030.MXBBP](#) [0315010.MXBP](#) [0315.062MXBP](#)
[031502.5MRT1BP](#) [0315012.MXBP](#) [0315007.MXBP](#)