


| SPECIFICATIONS | | |
|--------------------------|--|--|
| SILIKROME® | GRADE | |
| | COMMERCIAL | MILITARY |
| Material | Silicone Rubber ASTM D 1418 | Silicone Rubber conforming to A-A-59588 Class II GR 50 |
| Temperature Range | -112°F to +400°F (-80°C to +204°C) | -160°F to +450°F (-106°C to +260°C) |
| | -112°F to +575°F (-80°C to +302°C) | |
| Shelf Life | 25 Years (minimum) | |
| Resistant to | Salt spray, sunlight, ozone, cleaning solutions, and most acids | |
| Physical Characteristics | Flexible, non-breakable, re-usable. Acts as shock mount. Protects against shattering. Easy to mount. | |



SECTION AA

| | | | |
|---|---------------------------|----------------|------------------|
| C | REDRAWN and MAT'L CHANGED | S. GOK | 05.28.09 |
| B | CAD COMPUTER GENERATED | | 01.10.03 |
| A | REDESIGNED & REDRAWN | NICK | 05.07.73 |
| REV. | DESCRIPTION | | DATE |
| MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION. | | ENG. S. GOK | 05.28.09 |
| MAT'L: SEE ABOVE | | DWN. NKS | 09.09.66 |
| TITLE: SILIKROMES® COLORED FILTERS FOR INCANDESCENT T-3 1/4 LAMPS | | CHKD. J. CELLA | 05.28.09 |
| COLOR: SPECIFY | APM-HEXSEAL CORPORATION | SCALE 4 : 1 | DWG. NO. 1813/27 |

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

APM HEXSEAL:

[1813/27](#) [1813/27 A2 C](#) [1813/27 B1 C](#) [1813/27 G1 C](#) [1813/27 LW1 C](#) [1813/27 R1 C](#) [1813/27 Y1 C](#)