




HONEYWELL
PART NUMBER

4

REV	DOCUMENT	CHANGED BY	CHECK
A	0016296	LKM 24OCT05	VA



ACTUATOR COLOR (B=BLACK,
G=GRAY, R=RED, W=WHITE)


CIRCUITRY (SEE TABLE)

BASE/BEZEL COLOR (B=BLACK,
G=GRAY, R=RED, W=WHITE)

NUMBER OF POLES
(1=SP-SINGLE POLE, USES TERMINAL 1-2-4)
(2=DP-DOUBLE POLE, USES TERMINALS 1-2-4 AND 5-6-8)

TERMINAL STYLE 7

.250 [6.35] WIDE QUICK
CONNECT TABS 7
.187 [4.76] WIDE QUICK
CONNECT TABS 7



	CIRCUIT MADE WITH ROCKER IN 5		
	POSITION 3 (1&2, 5&6)	POSITION 2	POSITION 1 (2&4, 6&8)
1	ON	OFF	ON
2	OFF	NONE	ON
3	ON	NONE	ON
4	(OFF)	NONE	ON
5	(ON)	OFF	ON
6	OFF	NONE	(ON)
7	(ON)	OFF	(ON)
8	(ON)	NONE	ON

ELECTRICAL RATING & APPROVALS 7	
FOR .250 WIDE TABS: 20A, 12V FOR .187 WIDE TABS: 15A, 12V	

- NOTES
- 1 - OPERATING TEMPERATURE RANGE: -40°F TO +185°F (-40°C TO +85°C)
 - 2 - ELECTRICAL LIFE: 50,000 CYCLES MOMENTARY, 100,000 CYCLES MAINTAINED.
 - 3 - MECHANICAL LIFE: 250,000 CYCLES MIN
 - 4 SEE DIAGRAM FOR CATALOGING SCHEME
 - 5 PARENTHESIS DENOTE MOMENTARY ACTION
 - 6 - SEALED TO IP67
 - 7 - TERMINAL WIDTH AND ELECTRICAL RATING DEPENDENT ON STYLE SELECTED

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ± 0.040
ONE PLACE .X ± 0.030
TWO PLACE .XX ± 0.015
THREE PLACE .XXX ± 0.015
FOUR PLACE .XXXX ± 0.005
ANGLES X ± 2

THIRD ANGLE PROJECTION

DRAWN CR 13 JUN 05
CHECK RJ 13 JUN 05

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY

Pro/ENGINEER 2D

Honeywell

TITLE SWITCH, ROCKER

SIZE B TYPE I DRAWING NAME FRN SERIES CHART 1 REV A

SCALE NTS SHEET 1 OF 1