



[Home](#)  
[About Us](#)

## Products

[Audio](#)  
[Video](#)  
[Lighting](#)  
[Data Connectors](#)  
[Industrial](#)

[Support](#)  
[News](#)  
[Sitemap](#)

## Search

☐ PRODUCTS  
ONLY

Search

© Neutrik® AG  
All rights reserved  
Legal Notices




Audio

## XX Series

[back](#)

### NC5MXX



#### Product

|                |      |
|----------------|------|
| Connector Type | XLR  |
| Gender         | male |

#### Electrical

|                              |                               |
|------------------------------|-------------------------------|
| Capacitance between contacts | ≤ 7 pF                        |
| Contact resistance           | ≤ 3 mΩ                        |
| Dielectric strength          | 1,5 kVdc                      |
| Insulation resistance        | > 2 GΩ (initial)              |
| Insulation resistance        | > 1 GΩ (after damp heat test) |
| Rated current per contact    | 7,5 A                         |
| Rated voltage                | 50 V                          |

#### Mechanical

|                  |                          |
|------------------|--------------------------|
| Cable O.D.       | 3.5 - 8.0 mm             |
| Insertion force  | ≤ 20 N                   |
| Withdrawal force | ≤ 20 N                   |
| Lifetime         | > 1000 mating cycles     |
| Wire size        | max. 1.0 mm <sup>2</sup> |
| Wire size        | max. 18 AWG              |
| Wiring           | Solder contacts          |
| Locking device   | latch lock               |

#### Material

|                 |                            |
|-----------------|----------------------------|
| Boot            | Polyuretan                 |
| Bushing         | Polyamide (PA 6 15% GR)    |
| Contact plating | 2 µm Ag over 2 µm Ni       |
| Contacts        | Brass (CuZn39Pb3)          |
| Insert          | Polyamide (PA 6.6 30 % GR) |
| Locking element | Zinc diecast (ZnAl4Cu1)    |
| Shell           | Zinc diecast (ZnAl4Cu1)    |
| Shell plating   | Nickel                     |
| Strain relief   | Polyacetal (POM)           |

#### Environmental

|                     |                           |
|---------------------|---------------------------|
| Flammability        | UL 94 HB                  |
| Standard compliance | IEC 61076-2-103           |
| Protection class    | IP 40                     |
| Solderability       | Complies with IEC 68-2-20 |
| Temperature range   | -30 °C to +80 °C          |