








Notes:

- Electrical Specifications:
 - Meets USB 2.0 Specification
 - Contact Resistance: 30 mOhm max.
 - Insulation Resistance: 1000 MOhm min. @ 100 VDC
 - Current Rating: 1.5 A max. at 25° C
 - Working Voltage: 30 V (RMS) max.
 - DWV: 500 VAC/60s at sea level
 - Operating Temperature: -40° C to +85° C

2. Material and Finish:

- Receptacle Housing and Protective Cover: Polyester, UL94 V-0, Color: Black
- Panel Nut: Brass, Finish: Nickel Plated
- Panel and Cover Gasket: Silicon, Color: White
- Tether: Polycarbonate, Color: Black
- USB Adaptor Insulator: PBT, UL94 V-0, Black
- USB Adaptor Metal Shell: Copper Alloy, Nickel Plated
- USB Adaptor Overmold material: PBT UL94 V-0, Color: Black
- USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel

3. Connector can be mounted to a maximum panel thickness of 3.2 mm.

4. IP67 rated when covered or fully mated with the appropriated mating connector

Directive 2002/95/EC RoHS Compliant

Version	Part Number
Plastic Version	17-210141
Metallized Plastic Version	17-210181

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°			Scale:	Dim. in mm		
	Name	Title	Approval Date			Autodesk Inventor	Material: See Notes			
							Receptacle + Cover Assembly Kit Both Sides Bayonet Receptacle Housing with USB Type A F/F Adaptor			
	c	3 x c	Jan/18/2013	Vincent Ke	2012	Date	Name	Drawing No.: 17K1A357		DIN A3
	b	1 x b	Oct/17/2012	Vincent ke	Draw.	Sept. 28	Vincent Ke			
	a	original			Appd.	Sept. 28	J. Chaudry			
Rev.	Changes	Date	Name	Norm						
				D-old			Part No.: SEE PART NUMBER TABLE		Sheet 1/1	
										