

General Purpose Center Cut Bolt Cutters



END VIEW

- Series 2000 Bolt Cutter
- Drop-forged jaws with center-cut blades. Heat treated for wear resistance and long cutting life
- Cuts soft, and medium/hard materials
- Maximum hardness of material to be cut: Brinell 300/Rockwell C31
- Toggle joints turn 50 lbs. hand pressure to 4000 lbs. of cutting pressure
- Precision cast, 1-piece, aluminum alloy handles with rubber grips

Cat No.	UPC No.	Approx. Weight				Soft Materials (Up to Brinell 200, Rockwell C15)		Hard Materials (Up to Brinell 300, Rockwell C31)		Replacement Cutterhead	
		Ibs	k	Inch	mm	Inch	mm	Inch	mm	Cat. No.	UPC No.
1490AC	037103040978	1.7	.8	14	356	5/16	8	1/4	6	1413AC	037103059543
0090AC	037103040985	2.4	1.1	18	457	3/8	10	5/16	8	0013AC	037103059550
0190AC	037103040992	4	1.8	24	610	7/16	11	3/8	10	0113AC	037103059567



DANGER

Never use any H.K. Porter cutters on
energized circuits, wire, or cable.