STFI11N60M2-EP

N-channel 600 V, 0.550 Ω typ., 7.5 A MDmesh™ M2 EP Power MOSFET in an I²PAKFP package

Datasheet - production data



I²PAKFP (TO-281)

Figure 1: Internal schematic diagram



Features

Order code	V_{DS}	$R_{DS(on)}$ max.	I_D
STFI11N60M2-EP	600 V	0.595 Ω	7.5 A

- Extremely low gate charge
- Excellent output capacitance (C_{OSS}) profile
- Very low turn-off switching losses
- 100% avalanche tested
- Zener-protected
- Fully insulated and low profile package with increased creepage path from pin to heatsink plate

Applications

- Switching applications

Description

This device is an N-channel Power MOSFET developed using MDmesh™ M2 EP enhanced performance technology. Thanks to its strip layout and an improved vertical structure, the device exhibits low on-resistance, optimized switching characteristics with very low turn-off switching losses, rendering it suitable for the most demanding very high frequency converters.

Table 1: Device summary

Order code	Marking	Package	Packaging
STFI11N60M2-EP	11N60M2EP	I²PAKFP (TO-281)	Tube

Contents

1 Electrical ratings

Table 2: Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{GS}	Gate-source voltage	± 25	V
I_D	Drain current (continuous) at T_C = 25 °C	7.5	A
I_D	Drain current (continuous) at T_C = 100 °C	4.7	A
I_{DM}(1)	Drain current (pulsed)	30	A
P_{TOT}	Total dissipation at T_C = 25 °C	25	W
dv/dt(2)	Peak diode recovery voltage slope	15	V/ns
dv/dt(3)	MOSFET dv/dt ruggedness	50	V/ns
V_{ISO}	Insulation withstand voltage (RMS) from all three leads to external heat sink (t = 1 s, T_C = 25 °C)	2.5	kV
T_{stg}	Storage temperature range	- 55 to 150	°C
T_j	Operating junction temperature range		

Notes:

(1)Pulse width limited by safe operating area.

(2)$I_{SD} \leq 7.5$ A, di/dt ≤ 400 A/µs; $V_{DS\ peak} < V_{(BR)DSS}$, V_{DD} = 400 V.

(3)$V_{DS} \leq 480$ V

Table 3: Thermal data

Symbol	Parameter	Value	Unit
$R_{thj\text{-}case}$	Thermal resistance junction-case max	5	°C/W
$R_{thj\text{-}amb}$	Thermal resistance junction-ambient max	62.5	°C/W

Table 4: Avalanche characteristics

Symbol	Parameter	Value	Unit
I_{AR}	Avalanche current, repetetive or not repetetive (pulse width limited by T_{jmax})	2.4	A
E_{AS}	Single pulse avalanche energy (starting T_j = 25 °C, $I_D = I_{AR}$; V_{DD} = 50 V)	115	mJ

2 Electrical characteristics

T_C = 25 °C unless otherwise specified

Table 5: On/off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	V_{GS} = 0 V, I_D = 1 mA	600			V
I_{DSS}	Zero gate voltage Drain current	V_{GS} = 0 V, V_{DS} = 600 V			1	µA
		V_{GS} = 0 V, V_{DS} = 600 V, T_C = 125 °C (1)			100	µA
I_{GSS}	Gate-body leakage current	V_{DS} = 0 V, V_{GS} = ±25 V			±10	µA
$V_{GS(th)}$	Gate threshold voltage	V_{DS} = V_{GS}, I_D = 250 µA	2	3	4	V
$R_{DS(on)}$	Static drain-source on-resistance	V_{GS} = 10 V, I_D = 3.75 A		0.550	0.595	Ω

Notes:

(1)Defined by design, not subject to production test.

Table 6: Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{iss}	Input capacitance	V_{DS}= 100 V, f = 1 MHz, V_{GS} = 0 V	-	390	-	pF
C_{oss}	Output capacitance		-	22	-	pF
C_{rss}	Reverse transfer capacitance		-	0.7	-	pF
$C_{oss\ eq.}$ (1)	Equivalent output capacitance	V_{DS} = 0 to 480 V, V_{GS} = 0 V	-	49	-	pF
R_G	Intrinsic gate resistance	f = 1 MHz, I_D = 0 A	-	6.5	-	Ω
Q_g	Total gate charge	V_{DD} = 480 V, I_D = 7.5 A, V_{GS} = 10 V (see *Figure 16: "Test circuit for gate charge behavior"*)	-	12.4	-	nC
Q_{gs}	Gate-source charge		-	2.1	-	nC
Q_{gd}	Gate-drain charge		-	7	-	nC

Notes:

(1)$C_{oss\ eq.}$ is defined as a constant equivalent capacitance giving the same charging time as C_{oss} when V_{DS} increases from 0 to 80% V_{DSS}

Table 7: Switching energy

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$E_{(off)}$	Turn-off energy (from 90% V_{GS} to 0% I_D)	V_{DD} = 400 V, I_D = 1 A, R_G = 4.7 Ω, V_{GS} = 10 V	-	2.5	-	µJ
		V_{DD} = 400 V, I_D = 3 A, R_G = 4.7 Ω, V_{GS} = 10 V	-	9	-	µJ

Table 8: Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	V_{DD} = 300 V, I_D = 3.75 A, R_G = 4.7 Ω, V_{GS} = 10 V (see *Figure 15: "Test circuit for resistive load switching times"* and *Figure 20: "Switching time waveform"*)	-	9	-	ns
t_r	Rise time		-	5.5	-	ns
$t_{d(off)}$	Turn-off-delay time		-	26	-	ns
t_f	Fall time		-	8	-	ns

Table 9: Source drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{SD}	Source-drain current		-		7.5	A
I_{SDM} (1)	Source-drain current (pulsed)		-		30	A
V_{SD} (2)	Forward on voltage	V_{GS} = 0 V, I_{SD} = 7.5 A	-		1.6	V
t_{rr}	Reverse recovery time	I_{SD} = 7.5 A, di/dt = 100 A/µs, V_{DD} = 60 V (see *Figure 17: "Test circuit for inductive load switching and diode recovery times"*)	-	192		ns
Q_{rr}	Reverse recovery charge		-	1.32		µC
I_{RRM}	Reverse recovery current		-	13.8		A
t_{rr}	Reverse recovery time	I_{SD} = 7.5 A, di/dt = 100 A/µs, V_{DD} = 60 V, T_j = 150 °C (see *Figure 17: "Test circuit for inductive load switching and diode recovery times"*)	-	262		ns
Q_{rr}	Reverse recovery charge		-	1.74		µC
I_{RRM}	Reverse recovery current		-	13.3		A

Notes:

(1)Pulse width is limited by safe operating area

(2)Pulsed: pulse duration = 300 µs, duty cycle 1.5%

2.1 Electrical characteristics (curves)

Figure 2: Safe operating area



Figure 3: Thermal impedance



Figure 4: Output characteristics



Figure 5: Transfer characteristics



Figure 6: Gate charge vs gate-source voltage



Figure 7: Static drain-source on-resistance



Figure 8: Capacitance variations



Figure 9: Turn-off switching energy vs drain current



Figure 10: Normalized gate threshold voltage vs temperature



Figure 11: Normalized on-resistance vs temperature



Figure 12: Normalized V(BR)DSS vs temperature



Figure 13: Output capacitance stored energy



Figure 14: Source-drain diode forward characteristics



3 Test circuits

Figure 15: Test circuit for resistive load switching times



Figure 16: Test circuit for gate charge behavior



Figure 17: Test circuit for inductive load switching and diode recovery times



Figure 18: Unclamped inductive load test circuit



Figure 19: Unclamped inductive waveform



Figure 20: Switching time waveform



4 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: ***www.st.com***. ECOPACK® is an ST trademark.

4.1 I²PAKFP (TO-281) package information

Figure 21: I²PAKFP (TO-281) package outline



Table 10: I²PAKFP (TO-281) mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	4.40		4.60
B	2.50		2.70
D	2.50		2.75
D1	0.65		0.85
E	0.45		0.70
F	0.75		1.00
F1			1.20
G	4.95		5.20
H	10.00		10.40
L1	21.00		23.00
L2	13.20		14.10
L3	10.55		10.85
L4	2.70		3.20
L5	0.85		1.25
L6	7.50	7.60	7.70

5 Revision history

Table 11: Document revision history

Date	Revision	Changes
12-Apr-2016	1	First release.
07-Oct-2016	2	Document status promoted from preliminary to production data.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.