




PART NO. ENG. NO.

02-06-1131	1855-(P901)	
02-06-1132	1855-(P901)L	
02-06-5137	1855-(P591)	OBSOLETE
02-06-5136	1855-(P591)L	OBSOLETE
02-06-5138	1855-(P561)	
02-06-5139	1855-(P561)L	
02-06-5130	1855-(P550)	
02-06-5135	1855-(P550)L	
02-06-5147	1855-(P228)	
02-06-5148	1855-(P228)L	
02-06-1141	1855-1(P901)	
NOT TOOLED	1855-1(P901)L	
02-06-1143	1855-(P901)1	



SCALE:10X



SCALE:10X

LEGEND

1855-*(****)*

BLANK=WITH LOCKING TABS
1=WITHOUT LOCKING TABS

P=PREPLATE
BLANK=POSTPLATE

FORM
BLANK=CHAIN
1=CHAIN WITH INTERLEAF
PAPER ON REEL.
L=LOOSE

FINISH CODE

NOTES:

1. MATERIAL: BRASS

2. FINISHES:

901 HOT TIN DIP (.00051)/.000020 MIN.

* 228 SELECT GOLD PLATE (.00075)/.000030 MIN. IN CONTACT AREA, SELECT TIN (.00250)/.000100 MIN. IN CRIMP AREA OVER (.00125)/.000050 MIN. NICKEL OVERALL, WITH .000010/(.000025) MAX. SELECT GOLD FLASH IN AREA INDICATED.

561 SELECT GOLD PLATE (.00076)/.000030 MIN. IN CONTACT AREA, (.00127)/.000050 MIN. NICKEL OVERALL.

591 SELECT GOLD PLATE (.00127)/.000050 MIN. IN CONTACT AREA, OVER (.00127)/.000050 MIN. NICKEL OVERALL WITH (.00025)/.000010 MAX. GOLD FLASH OVERALL.


550 SELECT GOLD PLATE (.00038)/.000015 MIN. IN CONTACT AREA, OVER (.00076)/.000030 MIN. NICKLE OVERALL WITH (.00025)/.000010 MAX. GOLD FLASH OVERALL.

* THE PRIMARY SHIPPING CARTON WILL BE LABELED, *COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC THIS LABEL MAY CONTAIN PRODUCT WITH TIN-LEAD.

3. PRODUCT SPECIFICATION: PS-02-0-6

4. PACKAGE INFORMATION: NOT AVAILABLE

5. TERMINAL FOR USE WITH (.157)/.062 DIA. SERIES HOUSINGS AND WILL ACCEPT 24 THRU 30 AWG WIRE WITH (.102/2.29)/.040/.090 INSULATION DIAMETER.



SECT. "A-A"

AP	REVISE SH/PL PLATE REDRAWN TO ME10 5/07/04 RHOLTS
AN	OBSOLETE P/N UCR2002-0270 COMERC 01/9/28
AM1	OBSOLETE -IP575J & -IP575L ECR UG 0558 6/3/15/95 RW
AM	REV. AND REDRAWN PER ECR 10372 SEP 6-17-87 RW

REV. MATL. SPEC/USTAT TO ME10 EC NO.: IUCP2004L-20097 DRW:RHOLTS 2004/05/14 CHKD: 2004/05/14 APPR:FSMITH 2004/05/18 REV	QUALITY SYMBOLS DESCRIPTION ▽ - 0 ▽C - 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 8:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		REVISE ON CAD ONLY		
				DIMENSION STYLE IN/MM		TITLE				
		4 PLACES	± .0005	± .0005	DRAWN BY	DATE	CRIMP TERMINAL, FEMALE (.157)/.062 DIA., BRASS FOR 24 THRU 30 GA. WIRE MOLEX INCORPORATED			
		3 PLACES	± .001	± .001	GEP	1987/09/17				
		2 PLACES	± 0.25	± .014	CHECKED BY	DATE				
		1 PLACE	± 0.35	± .014	RW	1987/09/17				
		ANGULAR ±1/2°			APPROVED BY	DATE	MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
		DRAFT WHERE APPLICABLE			RAS	1987/09/17	SEE CHART	SD-1855-*	1 OF 1	
		MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					C