


6×6mm TACT Switch (Radial)

SKHV Series

Advantage in excellent mounting efficiency. Ground terminal version is also available.



Car Use

Features

- Supplied with radial taping.
- Allows automatic insertion onto PC board with the radial auto insertion machine.

Applications

- For operating various electronic devices such as audio devices, office equipment, communication devices, TVs, video recorders, automotive sets, etc.

Products Line

Vertical Type

Products No.	Operating force	Operating direction	Travel (mm)	Rating (max.)	Operating life (5mA 5V DC)	Initial contact resistance	Stem color	Stem height	Drawing No.	
SKHVBAD010	0.98N	Vertical	0.25	50mA 12V DC	1,000,000 cycles	100mΩ max.	Black	h=4.3mm	1	
SKHVBBD010	1.57N				500,000 cycles		Dark gray			
SKHVBCE010	2.55N				200,000 cycles		Red			
SKHVBDD010	0.98N				1,000,000 cycles		Black	h=5mm		
SKHVBED010	1.57N				500,000 cycles		Dark gray			
SKHVBFD010	2.55N				200,000 cycles		Red			
SKHVCED010	5.10N				1,000,000 cycles		Yellow	h=7mm		
SKHVBKD010	0.98N				500,000 cycles		Black			
SKHVBLD010	1.57N				200,000 cycles		Dark gray			
SKHVBMD010	2.55N				1,000,000 cycles		Red	h=9.5mm		
SKHVBGD010	0.98N				500,000 cycles		Black			
SKHVBHD010	1.57N				200,000 cycles		Dark gray			
SKHVBJD010	2.55N				1,000,000 cycles		Red			

With Ground Terminal Type

Products No.	Operating force	Operating direction	Travel (mm)	Rating (max.)	Operating life (5mA 5V DC)	Initial contact resistance	Stem color	Stem height	Drawing No.	
SKHVPAD010	0.98N	Vertical	0.25	50mA 12V DC	1,000,000 cycles	100mΩ max.	Black	h=4.3mm	2	
SKHVPBD010	1.57N				500,000 cycles		Dark gray			
SKHVPCE010	2.55N				200,000 cycles		Red			
SKHVPDD010	0.98N				1,000,000 cycles		Black	h=5mm		
SKHVPED010	1.57N				500,000 cycles		Dark gray			
SKHVPFD010	2.55N				200,000 cycles		Red			
SKHVPKD010	0.98N				1,000,000 cycles		Black	h=7mm		
SKHVPPLD010	1.57N				500,000 cycles		Dark gray			
SKHVPMD010	2.55N				200,000 cycles		Red			
SKHVPGD010	0.98N				1,000,000 cycles		Black	h=9.5mm		
SKHVPHD010	1.57N				500,000 cycles		Dark gray			
SKHVPJD010	2.55N				200,000 cycles		Red			

Power

Push

Slide

Rotary

Encoders

Detector

Dual-in-line
Package Type

Multi Control
Devices

TACT

Custom-
Products

Sharp
Feeling

Soft
Feeling

Snap-in
Type

Surface
Mount Type

Radial
Type

For detailed specifications, see P.415

For soldering conditions, see P.416

For specifications for the taping package, see P.419

Dimensions

Unit:mm

Power
Push
Slide
Rotary
Encoders
Detector
Dual-in-line
Package Type
Multi Control
Devices

TACT

Custom-
Products

Sharp
Feeling

Soft
Feeling


Snap-in
Type

Surface
Mount Type

Radial
Type

No.	Style	PC board mounting hole dimensions (Viewed from switch mounting face)										
1	<p>Vertical type</p> <table border="1"> <thead> <tr> <th>h</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>4.3</td> <td>3.5</td> </tr> <tr> <td>5</td> <td>3.5</td> </tr> <tr> <td>7</td> <td>3.3</td> </tr> <tr> <td>9.5</td> <td>3</td> </tr> </tbody> </table>	h	A	4.3	3.5	5	3.5	7	3.3	9.5	3	
h	A											
4.3	3.5											
5	3.5											
7	3.3											
9.5	3											
2	<p>With ground terminal type</p> <table border="1"> <thead> <tr> <th>h</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>4.3</td> <td>3.5</td> </tr> <tr> <td>5</td> <td>3.5</td> </tr> <tr> <td>7</td> <td>3.3</td> </tr> <tr> <td>9.5</td> <td>3</td> </tr> </tbody> </table>	h	A	4.3	3.5	5	3.5	7	3.3	9.5	3	
h	A											
4.3	3.5											
5	3.5											
7	3.3											
9.5	3											

Circuit Diagram



Note

Using a 1.6mm thick PC board is recommended.

Products Specifications

Items	Series	Sharp feeling type	Soft feeling type
Operating temperature range	-20°C to +70°C		
	-30°C to +85°C SKRM/RW		-30°C to +80°C SKPG
	-30°C to +90°C SKRA/RG/RP		-40°C to +90°C SKPF/PL/PM/PN
Rating (max.)		50mA 12V DC SKRP : 50mA 16V DC	5mA 12V DC SKPL/PM/PN : 50mA 16V DC
Rating (min.)		10 μ A 1V DC	
Electrical performance	Insulation resistance	100M Ω min. 100V DC SKEY/PD : 50M Ω min. 100V DC	
	Voltage proof	250V AC for 1 min. SKRB/RH/RM/RW/RR/EY/PD : 100V AC for 1min.	
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2 hours respectively	
	Lifetime	Shall be in accordance with individual specifications.	
Environmental performance	Cold	-30±2°C for 96h	
	Dry heat	80±2°C for 96h	
	Damp heat	60±2°C, 90 to 95%RH for 96h	

Note

We can raise the working temperature range for in-vehicle applications upon request. Contact us if you have any requirements of this kind.

Specifications of LED (SKHJ)

Color of light	Power dissipation P (mW)	Forward pulse peak current IFP (mA)	Forward current IFDC (mA)	Reverse voltage VR (V)	Forward voltage VF (V) IF=10mA	Reverse current IR (μ A) VR=4V	Peak emission wave length λ peak (nm) IF=10mA	Spectral line half width $\Delta \lambda$ (nm) IF=10mA	Luminous intensity IV (mcd) IF=10mA
Red	40	80	15	4	2.7 max. 2.05TYP	5 max.	700 TYP	100 TYP	0.4min. 1.0 TYP
Pure green							555 TYP	20 TYP	0.8min. 2.0 TYP
Amber							590 TYP	30 TYP	0.4min. 1.0 TYP
Orange (High brightness)				3	2.7 max. 2.0 TYP	10 max.	630 TYP	40 TYP	1.5min. 4.0 TYP
Green (High brightness)							565 TYP	30 TYP	2.0min. 5.0 TYP

Power

Push

Slide

Rotary

Encoders

Detector

Dual-in-line
Package TypeMulti Control
Devices

TACT


Custom-
ProductsSharp
FeelingSoft
FeelingSnap-in
TypeSurface
Mount TypeRadial
Type

Soldering Conditions

Condition for Reflow

Available for Surface Mount Type. (Except SKHM, SKHU, SKRM, SKRR Series)

1. Heating method: Double heating method with infrared heater.
2. Temperature measurement: Thermocouple 0.1 to 0.2 ϕ CA (K) or CC (T) at soldering portion (copper foil surface). A heat resisting tape should be used for fixed measurement.
3. Temperature profile



Notes

1. The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.
2. Soldering conditions differ depending on reflow soldering machines. You are requested to verify the soldering conditions thoroughly beforehand.

Conditions for Auto-dip

Available for Snap-in Type and Radial Type

(Except SKHJ, SKHL, SKQC, SKQJ, SKQK, SKEG series)

Items	Condition
Flux built-up	Mounting surface should not be coated with flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Continuous dipping time	5s max.
Number of soldering	2times max.

Manual Soldering

Available for Manual Soldering Type

Items	Condition
Soldering temperature	350°C max.
Continuous soldering time	3s max.

Notes

1. Consult with us for TACT switch washing conditions.
2. Prevent flux penetration from the top side of the TACT switch.
3. Switch terminals and a PC board should not be coated with flux prior to soldering.
4. The second soldering should be done after the switch returns to normal temperature.
5. Use the flux with a specific gravity of at least 0.82.
(EC-19s-8 by TAMURA Corporation, or their equivalents.)


Specification of Radial Taping Package

Taping Packaging for Auto-insertion

The SKHV, SKQC, SKQK, SKQN, SKQW, SKRC, SKRG, SKRS, SKPD and SKPL series are delivered with taping packaging.

Box Size

Unit:mm



Series	A	B	C
SKHV SKQC SKQK SKRS SKPD SKQN	47	331	291
SKQW	61		
SKRGAL to AS	48		
SKRGAA to AF	43	334	235
SKPL			340
SKRC	55	337	370

Quantity Accommodated Per Box

Series	Qty/reel (pcs.) (Minimum packing unit)
SKHV SKQK	1,000
SKQW SKRS	700
SKQC	1,500
SKPD	800
SKRG	2,000
SKQN SKRC	900
SKPL	2,700

Power

Push

Slide

Rotary

Encoders

Detector

Dual-in-line
Package TypeMulti Control
Devices

TACT

Custom-
ProductsSharp
FeelingSoft
FeelingSnap-in
TypeSurface
Mount TypeRadial
Type