

BZG1-2RN234

M

DRAWING
NUMBER

X

ISSUE
4

REVISIONS

A	C065843	TSM	3 NOV 89
B	C072977	GJW	8 AUG 92
C	C081513B	JAK	11 MAR 97

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK


CHECK

CHECK




ELASTOMER PLUNGER SEAL SECURED TO COMPONENTS
BY EXTERNAL BANDING

ROLLER LEVER IS SHOWN IN ITS FREE POSITION
AT ONE EXTREME OF ITS ADJUSTABLE RANGE



ROLLER LEVER MAY BE POSITIVELY
LOCKED AT INTERVALS OF APPROX
0.2° WITHIN A RANGE OF 225°
(1238 POSITIONS)

HEX SEAL NUT .938 REF ACROSS FLATS



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE - - - - - 14-26 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE - - - - - 10 OZ MIN	15A - 125, 250 OR 480 VAC; 2A - 600 VAC	UNLESS OTHERWISE NOTED
PRETRAVEL - - - - - .188 MAX	1 8HP-125 VAC; 1/4HP-250 VAC	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL - - - - - .006 MAX	CODE L74 1 2A-125 VDC; 1 4A 250 VDC	TOLERANCES ARE:
OVERTRAVEL - - - - - .219 MIN		ONE PLACE (.0) ±.030
SWITCH - BASIC REPLACEMENT - - - BZ-2RN7027		TWO PLACE (.00) ±.015
		THREE PLACE (.000) ±.005
		ANGLES ±
		WEIGHT

NOTES

1 - 6-32 UNC X .219 REF BINDING HEAD TERMINAL SCREW AND CUPWASHER (3)

2 - ROLLER LEVER BRACKET ASSEMBLY MAY BE SET AT ANY
POSITION AROUND AXIS OF PLUNGER

FORMTEK

DRAWN

T J O

17 JUL 89