

"High Frequency Ceramic Solutions"

5.5 GHz Band Pass Filter

Detail Specificat 02/13/03

P/N 5512BP15C725

Page 1 of 2


General Specifications

Part Number	5512BP15C725
Frequency (MHz)	5150 - 5875
Insertion Loss	2.5 dB max.
Return Loss	9.5 dB min.
Attenuation (min.)	30 dB @ 500-4000 MHz
Attenuation (min.)	20 dB @ 4600 MHz
Attenuation (min.)	15 dB @ 10.3-11.8 GHz

Input Power	500 Milliwatts max.
Impedance	50 Ω
Operating Temperature	-40 to +85°C
Reel Quantity	3,000


Terminal Configuration

No.	Function
1	GND
2	OUT
3	GND
4	IN



Mechanical Dimensions

	In	mm
L	0.079 $\pm$ 0.006	2.00 $\pm$ 0.15
W	0.049 $\pm$ 0.004	1.25 $\pm$ 0.10
T	0.037 $\pm$ 0.004	0.95 $\pm$ 0.10
a	0.051 $\pm$ 0.006	1.30 $\pm$ 0.15
b	0.012 $\pm$ 0.006	0.30 $\pm$ 0.15
c	0.010 $\pm$ 0.006	0.25 $\pm$ 0.15
d	0.014 $\pm$ 0.006	0.35 $\pm$ 0.15




Mounting Considerations

Mount these devices with brown mark facing up.

Line width should be designed to provide 50 Ω impedance matching characteristics.

Units: mm



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

931 Via Alondra • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

©2003 Johanson Technology, Inc. All rights reserved.

"High Frequency Ceramic Solutions"


5.5 GHz Band Pass Filter

P/N 5512BP15C725

Detail Specificat 02/13/03

Page 2 of 2

Typical Electrical Performance



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

931 Via Alondra • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

©2003 Johanson Technology, Inc. All rights reserved.