

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH-BASIC**

CATALOG LISTING

BE-2R-P4**BE-2R-P4****M**DRAWING
NUMBERISSUE
10

REPLACES

RELEASE NO. PR-3663

CHECK

REVISIONS

A	DES DGC CO-46317 SMA 20 AUG 79
B	REINST PRI1041 WJM 16 MAR 82
C	CO- 58782 WJM 23 JAN 86
D	CO- 73287-6 JAL 20 OCT 93
E	CO- 753678 K D R 3 MAR 94
F	CO- 77863 G J W 30 APR 96


CHECK

23 MAR 82

CEB

CHECK


16 MAR 82

DRAWN
WJM**NOTES**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $.139$ MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE ----- 14-22 OZ

RELEASE FORCE ----- 10 OZ MIN

DIFFERENTIAL TRAVEL --- .0020-.0075

OVERTRAVEL ----- .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

25A-125, 250, 480VAC
1HP-125VAC; 2HP-250 or 480VAC
PILOT DUTY 750VA-480VAC, MAX
60/75°C (Cu)



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. DIMENSIONS ARE IN INCHES UNLESS NOTED. TOLERANCES ARE:

	FRACTIONS	DECIMALS	ANGLES	RADIUS
NUM PLACES	1	3	1	1
NUM PLACES	1	3	1	1
NUM PLACES	1	3	1	1
NUM PLACES	1	3	1	1

DESIGN UNITS

INCHES

MILLIMETERS

WEIGHT .063 LB