


PRODUCT NO.	"A"	"B"	PLATING
88333-040	38	40.8	OBSOLETE
88333-044	42	44.8	OBSOLETE
88333-050	48	50.8	OBSOLETE
88333-150	48	50.8	OBSOLETE
88333-440LF	38	40.8	SEE NOTE ②
88333-444LF	42	44.8	
88333-450LF	48	50.8	
88333-140LF	38	40.8	SEE NOTE ②
88333-144LF	42	44.8	
88333-150LF	48	50.8	
88333-040LF	38	40.8	
88333-044LF	42	44.8	SEE NOTE ②
88333-050LF	48	50.8	
			CUSTOMER SPECIAL



NOTE:

- ① MATERIAL:HOUSING --- G.F.PBT
UL 94V-0. BLACK
TERMINAL --- PHOSPHOR BRONZE.

② 88333 - X XX

40, 44, 50 : 2X20, 2X22, 2X25
NUMBER OF CONTACTS.
0 : CONTACT AREA GOLD 0.2umMIN.
SOLDERTAIL TIN/LEAD 2.5umMIN.
1 : CONTACT AREA GOLD 0.76umMIN.
SOLDERTAIL TIN/LEAD 2.5umMIN.


88333 - X XX LF

LF PRODUCT NUMBER MEETS EUROPIAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

40, 44, 50 : 2X20, 2X22, 2X25
NUMBER OF CONTACTS.

1 : CONTACT AREA GOLD 0.76umMIN.
SOLDERTAIL PURE-TIN 2umMIN.
4 : CONTACT AREA GOLD 0.2umMIN.
SOLDERTAIL PURE-TIN 2umMIN.
0 : CUSTOMER SPECIAL PART NUMBER
CONTACT AREA GOLD 0.2umMIN.
SOLDERTAIL Sn-Cu 1.5umMIN.

- ③ CUT SURFACE IS UNPLATED.
④ GENERAL TOLERANCE:±0.25
⑤ FEATURE OF 2X25 POSITIONS : SEE FIG.1.
⑥ PRODUCT NUMBERS WITH "LF" SUFFIX WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 10 SECONDS IN WAVE SOLDER,
INFRA-RED OR VAPOR PHASE SOLDER PROCESS.



STAND-OFF FEATURE OF 2X25 POSITIONS.
© FIG.1

(SCALE 2.5/1)

mat'l. code SEE_NOTE_1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection mm	product family 5MWF - MINITEK RECEPTACLE	CODE JP
ltr	description	ecn no	dr	date	angles	linear	mm	MINITEK HCC	
D	REVISED	J05-0576	R.S	2006-1-31		0.X ±0.25			
E	REVISED	J06-0115	R.S	2006-4-16		0.XX ±0.25		dwg no sheet 1 of 1 size 88333 A3	
F	REVISED	J06-0352	R.S	2006-8-29	0'±X'	0.XXX ±0.25	scale 5:1		
G	REVISED	J08-0471	S.W	2008-12-8	dr	S. Nishida 2010-7-15		type Product Customer Drawing	
H	REVISED	J10-0118	S.W	2010-5-7	enr	S. Nishida 2010-7-15			
J	REVISED	J10-0192	S.W	2010-7-15	chr	M. Nishida 2010-7-15		Rev. J	
					appd	M. Nishida 2010-7-15			
sheet index	revision sheet	J	1						