




NOTES:

1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION

2 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 5 mm

3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
INDIVIDUALLY PACKED ASSEMBLY

4 DAT LABEL INFO:
- UNIQUE SERIAL NUMBER
- TYCO LOGO PN
- MANUFACTURING LOCN.

5 BLANK LABEL

6 NON CROSS OVER AS PER BELOW TABLE

LEFT CONN.	RIGHT CONN.
SC CONN. A	SC CONN. B
SC CONN. B	SC CONN. A

7 CABLE INFO:

CORE DIA - 50/125 μ m
OUTER DIA - 2,5 mm
JACKET COLOR - GOLD METALLIC
JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-6536464-Y	XY,0
8-6536464-1	0,6
9-6536464-1	1,5
9-6536464-2	2,5
9-6536464-3	3,5
9-6536464-4	4,5
9-6536464-9	9,5

2	-	FOAC DAT-85 LABEL	8
4	-	PROTECTIVE COVER, 2.5MM, BLACK	7
2	-	SC DUPLEX HOUSING. BEAM HALF	6
2	-	SC DUPLEX HOUSING, RET. PLATE HALF	5
4	-	SC CERAMIC, OVERMOLDED	4
4	-	CRIMP EYELET, SC, 2.0MM PLATED	3
4	-	FOAC STRAIN RELIEF, SC/FC BEIGE	2
L	-	FOCAB 50/125 TZ 2.5S OM3 GOLD	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16 DEC 05 CHK 16 DEC 05 APVD 16 DEC 05	Tyco Electronics Corporation Tyco Electronics FOBU, Bangalore, India	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ - 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ - FINISH	NAME - FOMM50 2,5S TZ OM3 DPX SC - SC -	
MATERIAL -		WEIGHT -	SIZE A2	RESTRICTED TO -
CUSTOMER DRAWING		SCALE NTS	DRAWING NO 00779	REV D