





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		F	EC 0G3C 0745 04	10JAN05	BSV	JRO
			F1	ECO-09-020932	26AUG09	KK	AEG



- 1
- 2
3.
- 4
- 5
6.
- 7
- 8
- 9
- 10
- PART NUMBER AND DATE CODE MARKED IN APPROXIMATE LOCATION SHOWN
- CONTACT: DUPLEX PLATED: .000010 GOLD ON CONTACT AREA, .000150-.000300 BRIGHT TIN-LEAD ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL.
- TOLERANCE IS NON-CUMULATIVE.
- POINT OF MEASUREMENT FOR PLATING THICKNESS (MEASURED INSIDE CONTACT BEAMS)
- POINT OF CONTACT MEASUREMENT.
- MATERIAL: HOUSING: GLASS FILLED POLYESTER-COLOR: BLACK
CONTACT: PHOSPHOR BRONZE
- CONTACT: DUPLEX PLATED: .000010 GOLD ON CONTACT AREA, .000150-.000300 MATTE TIN ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL.
- ROHS 2002/95/EC COMPLIANT
- TYCO LOGO AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

		52	1,2,29&30	1,2,29&30		3.000	2.900	60	5-102766-4
OBSOLETE		44	1,2,25&26	1,2,25&26		2.600	2.500	52	5-102766-3
		30	1,2,18&19	1,2,18&19		1.900	1.800	38	5-102766-2
		40	1,2,23&24	1,2,23&24		2.400	2.300	48	5-102766-1
		52	1,2,29&30	1,2,29&30		3.000	2.900	60	102766-4
OBSOLETE		44	1,2,25&26	1,2,25&26		2.600	2.500	52	102766-3
		30	1,2,18&19	1,2,18&19		1.900	1.800	38	102766-2
	SUPERCEDED	40	1,2,23&24	1,2,23&24		2.400	2.300	48	102766-1
	NO ACTIVE POS	ROW Y	ROW Z	FINISH	A	B	NO OF POSN	PART NO	
		CONTACTS OMITTED							

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

CONTACTS: SEE TABLE

DWN 14-5-81

CHK 15-5-81

APVD 20-5-81

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

NAME

CONNECTOR ASSY., MOD II/IV

DOUBLE ROW, .100 X .100 C/L, VERTICAL MOUNTED

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=102766

SCALE 4:1

SHEET 1 OF 1

REV F1