


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS					DOC. NO.	SPC-F005	Effective: 12/21/98		DCP No. 68
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRD	DATE	
	A	Rerdrawn in AutoCad	JAP	11/12/91					
1116	B	Was Dwg #CCS-TO-1*1*-HT	JWM	6/01/01	JC	6/20/01	JC	6/20/0	



PART NO.	WIRE RANGE (AWG)	DIAMETER 'B'	L	C	WALL THICK-NESS
CCS-TO-1010-HT	12-10	.135	.56	.28	.040
CCS-TO-1414-HT	16-14	.090	.56	.28	.030
CCS-TO-1818-HT	22-18	.070	.56	.28	.030

NOTES:

1. MATERIAL: ALLOY STEEL
FINISH: NICKEL PLATING
2. CONTINUOUS OPERATING TEMPERATURE:
900°F (482°C)
INTERMITTENT OPERATING TEMPERATURE:
1200°F (649°C)
3. VOLTAGE RATING: 600 V.

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF ELECTRONIC PARTS FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Tolerances: Unless Otherwise Specified: .X = ±.015 .XX = ±.010 .XXX = ±.005				DRAWING TITLE: High-Temperature Butt Connectors							
DRAWN BY:		DATE:		SIZE		DWG. NO.		ELECTRONIC FILE		REV	
JC		3/4/91		A		TA-350		TA-350.dwg		B	
CHECKED BY:		DATE:		JC		11/21/91					
APPROVED BY:		DATE:		JL		11/21/91					
SCALE: NTS		U.O.M.: INCHES [mm]		SHEET: 1		OF 1					