



DRG No. CP32943	ISSUE 1	TYPE No. OXL/CLH/100/P/FLxx/- OXL/CLH/100/P/CL/FLxx/-		DIM. IN: MILLIMETRES	ODC:QS:40077 ISSUE 1 DO NOT SCALE	THIS DRAWING AND THE COPYRIGHT AND DESIGN RIGHT THEREIN ARE THE PROPERTY OF OXLEY DEVELOPMENTS CO. Ltd. AND MUST NOT BE REPRODUCED OR DISCLOSED TO A THIRD PARTY WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ISS	MODIFICATION	DATE																																										
© COPYRIGHT OXLEY DEVELOPMENTS Co. Ltd. 2001																																																			
																																																			
<table><tr><th colspan="2">MATERIALS AND FINISHES</th></tr><tr><th>DESCRIPTION</th><th>MATERIAL, FINISH</th></tr><tr><td>BODY</td><td>ALUMINIUM ALLOY, MATT BLACK ANODISED</td></tr><tr><td>LENS</td><td>POLYCARBONATE</td></tr><tr><td>TERMINATIONS</td><td>FLYING LEADS : COLOUR RED AND BLACK WIRE INSULATION. LENGTH DEFINED IN PART No. (cm)</td></tr><tr><td>NUT</td><td>ALUMINIUM ALLOY</td></tr><tr><td>WASHER</td><td>BeCu. TIN PLATED</td></tr></table>							MATERIALS AND FINISHES		DESCRIPTION	MATERIAL, FINISH	BODY	ALUMINIUM ALLOY, MATT BLACK ANODISED	LENS	POLYCARBONATE	TERMINATIONS	FLYING LEADS : COLOUR RED AND BLACK WIRE INSULATION. LENGTH DEFINED IN PART No. (cm)	NUT	ALUMINIUM ALLOY	WASHER	BeCu. TIN PLATED																															
MATERIALS AND FINISHES																																																			
DESCRIPTION	MATERIAL, FINISH																																																		
BODY	ALUMINIUM ALLOY, MATT BLACK ANODISED																																																		
LENS	POLYCARBONATE																																																		
TERMINATIONS	FLYING LEADS : COLOUR RED AND BLACK WIRE INSULATION. LENGTH DEFINED IN PART No. (cm)																																																		
NUT	ALUMINIUM ALLOY																																																		
WASHER	BeCu. TIN PLATED																																																		
<table><tr><th colspan="6">ELECTRICAL / OPTICAL CHARACTERISTICS</th></tr><tr><th></th><th>AlGaAs RED</th><th>YELLOW</th><th>GREEN</th><th>BLUE</th><th>WHITE</th></tr><tr><td>LUMINOUS INTENSITY TYPICAL (mcd AT RATED VOLTAGE)</td><td>1200</td><td>1000</td><td>1250</td><td>1200</td><td>1000</td></tr><tr><td>WAVELENGTH TYPICAL (nm)</td><td>637</td><td>585</td><td>525</td><td>470</td><td>N/A</td></tr><tr><td>FORWARD CURRENT (mA) TYP</td><td>20</td><td>20</td><td>20</td><td>20</td><td>20</td></tr><tr><td>FORWARD VOLTAGE (V)</td><td>1.9</td><td>1.9</td><td>3.6</td><td>3.6</td><td>3.6</td></tr><tr><td>REVERSE VOLTAGE (V) MAX</td><td colspan="5">5</td></tr></table>							ELECTRICAL / OPTICAL CHARACTERISTICS							AlGaAs RED	YELLOW	GREEN	BLUE	WHITE	LUMINOUS INTENSITY TYPICAL (mcd AT RATED VOLTAGE)	1200	1000	1250	1200	1000	WAVELENGTH TYPICAL (nm)	637	585	525	470	N/A	FORWARD CURRENT (mA) TYP	20	20	20	20	20	FORWARD VOLTAGE (V)	1.9	1.9	3.6	3.6	3.6	REVERSE VOLTAGE (V) MAX	5							
ELECTRICAL / OPTICAL CHARACTERISTICS																																																			
	AlGaAs RED	YELLOW	GREEN	BLUE	WHITE																																														
LUMINOUS INTENSITY TYPICAL (mcd AT RATED VOLTAGE)	1200	1000	1250	1200	1000																																														
WAVELENGTH TYPICAL (nm)	637	585	525	470	N/A																																														
FORWARD CURRENT (mA) TYP	20	20	20	20	20																																														
FORWARD VOLTAGE (V)	1.9	1.9	3.6	3.6	3.6																																														
REVERSE VOLTAGE (V) MAX	5																																																		
<table><tr><th colspan="2">MOUNTING DETAILS</th></tr><tr><td colspan="2">MOUNTING HOLE : Ø10.15±0.1</td></tr><tr><td colspan="2">RECOMMENDED MOUNTING TORQUE : 1Nm</td></tr><tr><td colspan="2">CHASSIS THICKNESS : 1.5mm (Min)</td></tr></table>							MOUNTING DETAILS		MOUNTING HOLE : Ø10.15±0.1		RECOMMENDED MOUNTING TORQUE : 1Nm		CHASSIS THICKNESS : 1.5mm (Min)																																						
MOUNTING DETAILS																																																			
MOUNTING HOLE : Ø10.15±0.1																																																			
RECOMMENDED MOUNTING TORQUE : 1Nm																																																			
CHASSIS THICKNESS : 1.5mm (Min)																																																			
ORDERING INFORMATION : WHEN ORDERING, STATE TYPE NUMBER, SPECIFYING FLYING LEAD LENGTH AND LED COLOUR e.g OXL/CLH/100/P/FL10/G FLYING LEAD LENGTH IN cm COLOUR (AL, Y, G, B or W) AlGaAs RED, RED, YELLOW, GREEN, BLUE or WHITE																																																			
<table><tr><td></td><td>Tel. 01229 582621 Fax. 01229 585090</td><td>OXLEY DEVELOPMENTS COMPANY LTD.</td><td>Ulverston Cumbria LA12 9QG ENGLAND</td><td>SCALE 2 : 1</td><td>TYPE No. OXL/CLH/100/P/FLxx/- OXL/CLH/100/P/CL/FLxx/-</td><td>DRG No. CP32943</td><td>ISSUE 1</td></tr></table>								Tel. 01229 582621 Fax. 01229 585090	OXLEY DEVELOPMENTS COMPANY LTD.	Ulverston Cumbria LA12 9QG ENGLAND	SCALE 2 : 1	TYPE No. OXL/CLH/100/P/FLxx/- OXL/CLH/100/P/CL/FLxx/-	DRG No. CP32943	ISSUE 1																																					
	Tel. 01229 582621 Fax. 01229 585090	OXLEY DEVELOPMENTS COMPANY LTD.	Ulverston Cumbria LA12 9QG ENGLAND	SCALE 2 : 1	TYPE No. OXL/CLH/100/P/FLxx/- OXL/CLH/100/P/CL/FLxx/-	DRG No. CP32943	ISSUE 1																																												
							MATERIAL AS STATED	DRAWN <i>Simon Ryssam</i>																																											
							FINISH AS STATED	CHECKED T. DAVIS																																											
							PLATING AS STATED	APPROVED DA01/351																																											
							TOLERANCE AS STATED	DATE 10 DEC 01																																											
							REMARKS																																												
							TITLE WIDE ANGLE HIGH BRIGHTNESS LED INDICATOR WITH PROMINENT LENS AND FLYING LEADS																																												