



CONNECTOR PRO SERIES 105 MALE

Contacts number nn	Length without latches in mm	
	A	C
02	2	7.4
03	4	9.4
04	6	11.4
05	8	13.4
06	10	15.4
07	12	17.4
08	14	19.4
09	16	21.4
10	18	23.4
11	20	25.4
12	22	27.4
13	24	29.4
14	26	31.4
15	28	33.4
16	30	35.4
17	32	37.4
18	34	39.4
19	36	41.4
20	38	43.4
21	40	45.4
22	42	47.4
23	44	49.4
24	46	51.4
25	48	53.4

Latch separation tool	P/N C14790
LF contacts insertion & withdrawal tool	P/N C12935
Recommended hand crimp tool	P/N MH800
Recommended positioner K1692	P/N C12929
AWG24 crimp tool setting	Position 7
AWG26 & AWG28 crimp tool setting	Position 6

Ce plan est la propriété exclusive de la société NICOMATIC.
Il ne peut être reproduit sans son autorisation. Loi du 11.03.1902.

This document and drawings, sketches, and schematic drawings are the property of the NICOMATIC company. and no parts thereof may be reproduced and used without the written consent of the owner.
Law dated 11.03.1902



TECHNICAL FEATURES

MATERIALS

INSULATOR : Glass filled thermoplastic UL 94-V0

CRIMPING SIGNAL CONTACTS :

Male : Brass / 0.3µ gold plated

FIXING HARDWARE :

- Latch : Beryllium copper / Ni 2µ nickel plated

ELECTRICAL


- All contacts: 3 A max. @ 25°C, 2.2 A max. @ 85°C, 300V AC/DC
- Working / Rated voltage (sea level): 400V AC/DC
- Proof / Withstanding voltage: max. 20 mΩ
- Contact resistance (initial): max. 25 mΩ
- Contact resistance (after conditioning): 1000 MΩ min
- Insulation resistance (initial): 500 cycles.

MECHANICAL


- Mechanical operations: 2N max. / 0.2 N min.
- Contact insertion and withdrawal force: 10N min.
- Contact retention in insulator

ENVIRONMENTAL

- Temperature range: From -55°C to +125°C, Peak Reflow Compatible 260°C
- RoHS: Yes



173, rue des fougères
Z.I. Les Bracots
F-74890 Bons-en-Chablais
Tel. : +33 (0)4.50.36.13.85
Fax : +33 (0)4.50.36.11.33
Web : www.nicomatic.com



Echelle/Scale

3:1

a	16/05/08	H.T.		D.Z.
Ind	Date	Drawn	Checked	Approved
Désignation : Connector CMM100 Pro series Male crimp AWG24-28				

105Snn(L)-cl
Réf. catalogue /
Catalogue Reference 105Snn(L)

Tolérance générale /
General tolerance ±0.2

Page
1/1

A4