



SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Insulator (Body): Thermoplastic (UL94V-0)
- Insulator (Cover): Thermoplastic (UL94V-0)
- Terminal screw: Steel Zinc plating "-" slot type
- Terminal body: Brass (CuZn) Zinc plating
- Contact Pin: Brass, Tin plated
- Flange nut: Brass

Electrical

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
 - Solid wire (AWG): 12-22
 - Stranded wire (AWG): 12-22
- Torque: 4Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C

RoHS Compliant

PART NUMBER:

OSTV8XX5151

No. of Poles
 02 2 Poles
 03 3 Poles
 ...
 24 24 Poles

COLOR
 0: Black
 5: Green (Standard)
 6: Blue
 8: Grey

Poles	2	3	4	5	6	7	8	9	10	11	12	13
Dim A	11.66	16.74	21.82	26.90	31.98	37.06	42.14	47.22	52.30	57.38	62.46	67.54
Dim B	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
TOL	±0.15					±0.20						
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	72.62	77.70	82.78	87.86	92.94	98.02	103.10	108.18	113.26	118.34	123.42	
Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	
TOL	±0.30					0.4						



TITLE		OSTV8 5.08 Series With flange A					
PART NO.	OSTV8XX5151			DWG NO.	OSTV8XX5151.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
Seamus	Seamus	Seamus	Tason		UNIT: mm		X. ±0.50
2008.10.17	2008.10.17	2008.10.17	2007.10.30		SCALE: NONE		X.X ±0.30
				SHEET: 01/01	REV: A	X° ±1°	