

82760 Multi-Conductor - Single-Pair Cable

 For more Information
 please call

1-800-Belden1

**Description:**

18 AWG stranded (19x30) TC conductors, plenum, FEP insulation, twisted pair, overall Beldfoil® shield (100% coverage), 20 AWG stranded TC drain wire, Flamarrest® jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
1	18	19x30	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
FEP - Fluorinated Ethylene Propylene	0.1778

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil® with shorting fold	Tape	Aluminum Foil-Polyester Tape	100.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	Stranded	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.3556

Overall Cabling

Overall Nominal Diameter: 3.708 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
Bulk Cable Weight:	33.485 Kg/Km
Max. Recommended Pulling Tension:	284.685 N
Min. Bend Radius (Install)/Minor Axis:	40.640 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes

82760 Multi-Conductor - Single-Pair Cable

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MIL Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	NFPA 262
----------------	----------

C(UL) Flame Test:	FT6
-------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Non-Plenum Number:	8760
--------------------	------

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

35

Nom. Inductance:

Inductance (μH/m)

0.49215

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

167.331

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

318.257

Nominal Velocity of Propagation:

VP (%)

69

Nominal Delay:

Delay (ns/m)

4.82307

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

18.0455

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

23.9513

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

5.4 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

METRIC MEASUREMENT VERSION

82760 Multi-Conductor - Single-Pair Cable

Item #	Putup	Ship Weight	Color	Notes	Item Desc
82760 877U1000	305 MT	9.525 KG	NATURAL		1 PR #18 FEP FS FLMRST
82760 877U500	152 MT	4.990 KG	NATURAL		1 PR #18 FEP FS FLMRST
82760 8771000	305 MT	9.072 KG	NATURAL	C	1 PR #18 FEP FS FLMRST
82760 8775000	1,524 MT	47.627 KG	NATURAL		1 PR #18 FEP FS FLMRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 05-26-2010

© 2011 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.