

Relays &amp; Contactors &gt; Electromechanical Relays

Relay & Contactor Type: **Time Delay Relay**Contact Arrangement: **2 Form C DPDT-CO**Current Type: **DC**Contact Current Rating: **10 A**Main Termination & Connection Type: **Solder Hook Terminals**

## Features

### Product Type Features

Relay & Contactor Type	Time Delay Relay
------------------------	------------------

### Configuration Features

Contact Arrangement	2 Form C DPDT-CO
---------------------	------------------

### Electrical Characteristics

Input Voltage	28 VDC
---------------	--------

Contact Current Rating	10 A
------------------------	------

### Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

### Contact Features

Contact Material	Silver Cadmium Oxide
------------------	----------------------

### Termination Features

Main Termination & Connection Type	Solder Hook Terminals
------------------------------------	-----------------------

Coil Termination & Connection Type	Solder Hook Terminals
------------------------------------	-----------------------

### Mechanical Attachment

Product Mounting Feature Type	Mounting Brackets
-------------------------------	-------------------

Product Mount Type	Chassis Mount
--------------------	---------------

### Dimensions

Product Width	25.79 mm[1.015 in]
Product Length	43.6 mm[1.717 in]
Product Height	25.4 mm[1 in]

### Usage Conditions

Operating Temperature Range	-55 – 125 °C
Environmental Ambient Temperature (Max)	125 °C[257 °F]

### Operation/Application

Indicator Type	No Indicator
Repeatability (Max)	±10%
Type of Control	Fixed
Mode of Operation	Delay on Operate
Delay Time	1 second
Current Type	DC

### Other

Contact Current Class	>5 – ≤10 A
Height Class (Mechanical)	>22 – ≤27 mm[>.866 – ≤1.063 in]
Length Class (Mechanical)	>33 – ≤45 mm[>1.299 – ≤1.772 in]
Width Class (Mechanical)	>22 – ≤33 mm[>.866 – ≤1.299 in]

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 9-1617748-2  
FCA-210-0919M=M83536/9-019M

## Customers Also Bought




TE Part #187788-000  
SO63-3-00



TE Part #314721-000  
382A034-100/180-0



TE Part #758539-000  
SO63-2-00



TE Part #806089-000  
202C642-71-0



TE Part #1-1616941-2  
A701DA=CUTOUT REVERSE  
CURRENT 400 AMP-28



TE Part #1617118-6  
J1MAC-26XP = M39016/7-030P



TE Part #358149-000  
201M144-19B



TE Part #2-1617003-9  
B07B932BZ1-8005 = 07 10AMP REL



## Documents

### Product Drawings

[TD228-1001S=TDF0 1SEC M83726/28-1001S](#)

English

---

### Datasheets & Catalog Pages

[High\\_Performance\\_Relays\\_Section5](#)

English

[relays\\_brochure](#)

English