

# tesa® 4943

Double-sided non woven tape

## PRODUCT INFORMATION

### Product Description

tesa® 4943 is a double-sided tape consisting of a non woven backing equipped with a solvent based tackified acrylic adhesive. It provides a high initial tack and a good shear resistance.

### Main Application

- Lamination of leather, textiles and foams
- Mounting of light parts such as signs, covers and nameplates
- Sealing of bags and envelops
- Splicing

### Technical Data

■ Backing material	non-woven	■ Elongation at break	2 %
■ Colour	translucent	■ Tensile strength	9 N/cm
■ Thickness of tape	100 µm	■ Type of liner	PE-coated paper
■ Type of adhesive	tackified acrylic	■ Colour of liner	white
■ Type of adhesive (covered side)	tackified acrylic	■ Thickness of liner	120 µm

### Adhesion to

■ Steel (initial)	5.5 N/cm	■ Steel (after 14 days)	8.1 N/cm
■ ABS (initial)	6.6 N/cm	■ ABS (after 14 days)	7.1 N/cm
■ Aluminium (initial)	3.6 N/cm	■ Aluminium (after 14 days)	4.2 N/cm
■ PC (initial)	7.7 N/cm	■ PC (after 14 days)	7.1 N/cm
■ PET (initial)	4.6 N/cm	■ PET (after 14 days)	5.4 N/cm
■ PS (initial)	6.9 N/cm	■ PVC (after 14 days)	10.8 N/cm
■ PVC (initial)	6.1 N/cm		

### Properties

■ Static shear resistance at 23 °C	++	■ Resistance to chemicals	o
■ Static shear resistance at 40 °C	++	■ Ageing resistance (UV)	+
■ Static shear resistance at 70 °C	+	■ Humidity resistance	+
■ Tack	+	■ Temperature resistance short term	100 °C
■ Fogging	+	■ Temperature resistance long term	70 °C

Evaluation across relevant tesa® assortment: ++ very good, + good, o medium, - low

#### tesa SE

Quickbornstraße 24  
20253 Hamburg  
Germany  
Phone: +49 (40) 4909 101

tesa SE

A Beiersdorf Company

<http://www.tesa.com>

#### tesa tape inc.

5825 Carnegie Boulevard  
Charlotte, N.C. 28209  
United States of America  
Phone: +1 (704) 554 0707  
Fax: +1 (704) 553 5634  
<http://www.tesatape.com>

#### tesa tape Asia Pacific Pte. Ltd.

164 Gul Circle,  
Singapore 629621  
Phone: +65 (68) 612 026  
Fax: +65 (68) 614 790  
<http://www.tesa-asia.com>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you.