

C1608X7R1E334K080AC (TDK item description : C1608X7R1E334KT**)**

Applications



Commercial Grade



Please refer to Part No. CGA3E3X7R1E334K080AB for automotive use.


Feature



General (Up to 50V)

Series

C1608 [EIA CC0603]



Size

Length(L)	1.60mm +/-0.10mm
Width(W)	0.80mm +/-0.10mm
Thickness(T)	0.80mm +/-0.10mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	0.30mm Min.
Recommended Land Pattern(PA)	0.70 to 1.00mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Land Pattern(PB)	0.80 to 1.00mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Land Pattern(PC)	0.60 to 0.80mm (Flow Soldering) 0.60 to 0.80mm (Reflow Soldering)
Recommended Slit Pattern(SD)	

Electrical Characteristics

Capacitance	330nF +/-10%
Rated Voltage	25Vdc
Temperature Characteristic	X7R(+/-15%)
Dissipation Factor	5% Max.
Insulation Resistance	303MΩ Min.

Other

Soldering Method	Reflow, Flow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.

C1608X7R1E334K080AC

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)

