




LOC	DIST	REVISONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GP	00	N1		REVISED PER ECO-11-004835	11MAR11	RK HMR



- 1 DOUBLE BAR POLARIZATION
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POSTS: GOLD FLASH OVER PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL ON THE MATING SUFACES, .000100 MIN TIN-LEAD PLATE ON THE SOLDER-TAILS, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
-OR-
.000030 MIN GOLD PLATE ON THE MATING SURFACES, .000100 MIN TIN-LEAD PLATE ON THE SOLDER-TAILS, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- 4 CENTER POLARIZATION SLOT
- 5 FOR 10 POSN ASSEMBLY, SLOT OMITTED WHERE INDICATED
- 6 OPTIONAL AMP IDENTIFICATION NUMBER (DATE CODE). LOCATION APPROXIMATELY WHERE SHOWN.
- 7 PACKAGED IN GANG OF TUBES.
- 8 NUMBER 1 POSITION.



RECOMMENDED HOLE LAYOUT
FOR MANUAL INSERTION

1	OBsolete	2.800	2.400	24	50	1-103309-8
2	OBsolete	1.500	1.100	11	24	1-103309-7
3	OBsolete	1.600	1.200	12	26	1-103309-4
4	OBsolete	1.300	.900	9	20	1-103309-3
5	OBsolete	3.300	2.900	29	60	1-103309-2
6	OBsolete	3.100	2.700	27	56	1-103309-1
7	OBsolete	2.800	2.400	24	50	1-103309-0
8	OBsolete	2.500	2.100	21	44	103309-9
9		2.300	1.900	19	40	103309-8
10		2.000	1.600	16	34	103309-7
11		1.600	1.200	12	26	103309-6
12		1.300	.900	9	20	103309-5
13	OBsolete	1.200	.800	8	18	103309-4
14		1.100	.700	7	16	103309-3
15		1.000	.600	6	14	103309-2
16		.800	.400	4	10	103309-1
17		C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. MOLL 8-27-87	TE TE Connectivity	
		CHK L. MEYER 9-03-87		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. FEIDT 9-03-87	NAME	
	0 PLC ± -	PRODUCT SPEC	HEADER ASSY, LOW PROFILE, AMP-LATCH	
	1 PLC ± -	108-40018	-	
	2 PLC ± -	APPLICATION SPEC		
MATERIAL: HOUSING: GLASS FILLED NYLON OR PBT, BLACK, UL 94V-0 RATED POSTS: BRASS	3 ANGLES FINISH	WEIGHT -	SIZE A1	CAGE CODE 00779
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1
			REV N1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103309-2](#)