




- 1

0.76µm [.000030] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
2.

PLATING THICKNESS TO BE MEASURED ON SURFACES ACCESSIBLE WITH 0.64 [.025] DIA SPHERE.
- 3

WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL-
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER-
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL
- 4

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE	SMALL PACK	202507-3
4 OBSOLETE	TAPE MTG (SEE DETAIL) 3	202507-2
	STANDARD	202507-1
	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ 04/07/93	TE TE Connectivity	
DIMENSIONS: MM[INCHES]		CHK R.STONE 4-26-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.S.KLINE 4-29-93	NAME	
0 PLC ± -		PRODUCT SPEC	CONTACT ASSEMBY, PIN, #16, 16-18 AWG, TYPE II	
1 PLC ± -		APPLICATION SPEC		
2 PLC ± -		—	SIZE CAGE CODE DRAWING NO	
3 PLC ± -		—	A2 00779 C-202507	
4 PLC ± -		—	RESTRICTED TO	
ANGLES ± ± -		—	—	
FINISH		WEIGHT	—	
MATERIAL		CUSTOMER DRAWING	SCALE 10:1 SHEET 1 of 1 REV F2	
PIN BODY: COPPER ALLOY				
SPRING: STAINLESS STEEL				
PIN BODY: 1				

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.