

# 1SMB5913BT3 Series

Preferred Device

## 3 Watt Plastic Surface Mount Zener Voltage Regulators

This complete new line of 3 Watt Zener diodes offers the following advantages.

### Specification Features

- Zener Voltage Range – 3.3 V to 200 V
- ESD Rating of Class 3 (>16 kV) per Human Body Model
- Flat Handling Surface for Accurate Placement
- Package Design for Top Side or Bottom Circuit Board Mounting
- Pb-Free Packages are Available

### Mechanical Characteristics

**CASE:** Void-free, transfer-molded plastic

**FINISH:** All external surfaces are corrosion resistant and leads are readily solderable

**MAXIMUM LEAD TEMPERATURE FOR SOLDERING PURPOSES:**  
260°C for 10 Seconds

**LEADS:** Modified L-Bend providing more contact area to bond pads

**POLARITY:** Cathode indicated by polarity band

**FLAMMABILITY RATING:** UL 94 V-0

### MAXIMUM RATINGS

| Rating                                                                                                                               | Symbol          | Value             | Unit                                              |
|--------------------------------------------------------------------------------------------------------------------------------------|-----------------|-------------------|---------------------------------------------------|
| Maximum Steady State Power Dissipation @ $T_L = 75^\circ\text{C}$<br>Measured at Zero Lead Length<br>Derate Above $75^\circ\text{C}$ | $P_D$           | 3.0               | W                                                 |
| Thermal Resistance from Junction-to-Lead                                                                                             | $R_{\theta JL}$ | 40<br>25          | mW/ $^\circ\text{C}$<br>$^\circ\text{C}/\text{W}$ |
| Maximum Steady State Power Dissipation<br>@ $T_A = 25^\circ\text{C}$ (Note )<br>Derate Above $25^\circ\text{C}$                      | $P_D$           | 550               | mW                                                |
| Thermal Resistance from Junction-to-Ambient                                                                                          | $R_{\theta JA}$ | 4.4<br>226        | mW/ $^\circ\text{C}$<br>$^\circ\text{C}/\text{W}$ |
| Operating and Storage<br>Temperature Range                                                                                           | $T_J, T_{stg}$  | -65<br>to<br>+150 | $^\circ\text{C}$                                  |

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.


1. FR-4 board, within 1" to device, using recommended footprint.



ON Semiconductor®


<http://onsemi.com>

## PLASTIC SURFACE MOUNT ZENER VOLTAGE REGULATOR DIODES 3.3–200 V, 3 W DC POWER



SMB  
CASE 403A  
PLASTIC

### MARKING DIAGRAM



Y = Year  
WW = Work Week  
9xxB = Specific Device Code  
(See Table page 3)

### ORDERING INFORMATION

| Device       | Package          | Shipping†        |
|--------------|------------------|------------------|
| 1SMB59xxBT3  | SMB              | 2500/Tape & Reel |
| 1SMB59xxBT3G | SMB<br>(Pb-Free) | 2500/Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


Preferred devices are recommended choices for future use and best overall value.

## 1SMB5913BT3 Series

### ELECTRICAL CHARACTERISTICS

( $T_L = 30^\circ\text{C}$  unless otherwise noted,  
 $V_F = 1.5\text{ V Max. @ } I_F = 200\text{ mA(dc)}$  for all types)

| Symbol   | Parameter                          |
|----------|------------------------------------|
| $V_Z$    | Reverse Zener Voltage @ $I_{ZT}$   |
| $I_{ZT}$ | Reverse Current                    |
| $Z_{ZT}$ | Maximum Zener Impedance @ $I_{ZT}$ |
| $I_{ZK}$ | Reverse Current                    |
| $Z_{ZK}$ | Maximum Zener Impedance @ $I_{ZK}$ |
| $I_R$    | Reverse Leakage Current @ $V_R$    |
| $V_R$    | Reverse Voltage                    |
| $I_F$    | Forward Current                    |
| $V_F$    | Forward Voltage @ $I_F$            |
| $I_{ZM}$ | Maximum DC Zener Current           |



# 1SMB5913BT3 Series

## ELECTRICAL CHARACTERISTICS (Devices listed in **bold, italic** are ON Semiconductor Preferred devices.)

(T<sub>L</sub> = 30°C unless otherwise noted, V<sub>F</sub> = 1.5 V Max. @ I<sub>F</sub> = 200 mA(dc) for all types)

| Device<br>(Note 2)     | Device<br>Marking | Zener Voltage (Note 3) |            |              |                   | Zener Impedance (Note 4)          |                                   |                                 | Leakage Current |             | I <sub>ZM</sub> |
|------------------------|-------------------|------------------------|------------|--------------|-------------------|-----------------------------------|-----------------------------------|---------------------------------|-----------------|-------------|-----------------|
|                        |                   | V <sub>Z</sub> (Volts) |            |              | @ I <sub>ZT</sub> | Z <sub>YT</sub> @ I <sub>ZT</sub> | Z <sub>ZK</sub> @ I <sub>ZK</sub> | I <sub>R</sub> @ V <sub>R</sub> |                 |             |                 |
|                        |                   | Min                    | Nom        | Max          | mA                | Ω                                 | Ω                                 | mA                              | μA              | Volts       | mA(dc)          |
| 1SMB5913BT3            | 913B              | 3.13                   | 3.3        | 3.47         | 113.6             | 10                                | 500                               | 1                               | 100             | 1           | 454             |
| 1SMB5914BT3            | 914B              | 3.42                   | 3.6        | 3.78         | 104.2             | 9                                 | 500                               | 1                               | 75              | 1           | 416             |
| <b>1SMB5915BT3</b>     | <b>915B</b>       | <b>3.70</b>            | <b>3.9</b> | <b>4.10</b>  | <b>96.1</b>       | <b>7.5</b>                        | <b>500</b>                        | <b>1</b>                        | <b>25</b>       | <b>1</b>    | <b>384</b>      |
| <b>1SMB5916BT3</b>     | <b>916B</b>       | <b>4.08</b>            | <b>4.3</b> | <b>4.52</b>  | <b>87.2</b>       | <b>6</b>                          | <b>500</b>                        | <b>1</b>                        | <b>5</b>        | <b>1</b>    | <b>348</b>      |
| <b>1SMB5917BT3</b>     | <b>917B</b>       | <b>4.46</b>            | <b>4.7</b> | <b>4.94</b>  | <b>79.8</b>       | <b>5</b>                          | <b>500</b>                        | <b>1</b>                        | <b>5</b>        | <b>1.5</b>  | <b>319</b>      |
| <b>1SMB5918BT3, G*</b> | <b>918B</b>       | <b>4.84</b>            | <b>5.1</b> | <b>5.36</b>  | <b>73.5</b>       | <b>4</b>                          | <b>350</b>                        | <b>1</b>                        | <b>5</b>        | <b>2</b>    | <b>294</b>      |
| <b>1SMB5919BT3, G*</b> | <b>919B</b>       | <b>5.32</b>            | <b>5.6</b> | <b>5.88</b>  | <b>66.9</b>       | <b>2</b>                          | <b>250</b>                        | <b>1</b>                        | <b>5</b>        | <b>3</b>    | <b>267</b>      |
| <b>1SMB5920BT3, G*</b> | <b>920B</b>       | <b>5.89</b>            | <b>6.2</b> | <b>6.51</b>  | <b>60.5</b>       | <b>2</b>                          | <b>200</b>                        | <b>1</b>                        | <b>5</b>        | <b>4</b>    | <b>241</b>      |
| 1SMB5921BT3            | 921B              | 6.46                   | 6.8        | 7.14         | 55.1              | 2.5                               | 200                               | 1                               | 5               | 5.2         | 220             |
| 1SMB5922BT3            | 922B              | 7.12                   | 7.5        | 7.88         | 50                | 3                                 | 400                               | 0.5                             | 5               | 6           | 200             |
| <b>1SMB5923BT3, G*</b> | <b>923B</b>       | <b>7.79</b>            | <b>8.2</b> | <b>8.61</b>  | <b>45.7</b>       | <b>3.5</b>                        | <b>400</b>                        | <b>0.5</b>                      | <b>5</b>        | <b>6.5</b>  | <b>182</b>      |
| 1SMB5924BT3            | 924B              | 8.64                   | 9.1        | 9.56         | 41.2              | 4                                 | 500                               | 0.5                             | 5               | 7           | 164             |
| <b>1SMB5925BT3</b>     | <b>925B</b>       | <b>9.5</b>             | <b>10</b>  | <b>10.5</b>  | <b>37.5</b>       | <b>4.5</b>                        | <b>500</b>                        | <b>0.25</b>                     | <b>5</b>        | <b>8</b>    | <b>150</b>      |
| <b>1SMB5926BT3</b>     | <b>926B</b>       | <b>10.45</b>           | <b>11</b>  | <b>11.55</b> | <b>34.1</b>       | <b>5.5</b>                        | <b>550</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>8.4</b>  | <b>136</b>      |
| <b>1SMB5927BT3, G*</b> | <b>927B</b>       | <b>11.4</b>            | <b>12</b>  | <b>12.6</b>  | <b>31.2</b>       | <b>6.5</b>                        | <b>550</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>9.1</b>  | <b>125</b>      |
| 1SMB5928BT3            | 928B              | 12.35                  | 13         | 13.65        | 28.8              | 7                                 | 550                               | 0.25                            | 1               | 9.9         | 115             |
| <b>1SMB5929BT3</b>     | <b>929B</b>       | <b>14.25</b>           | <b>15</b>  | <b>15.75</b> | <b>25</b>         | <b>9</b>                          | <b>600</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>11.4</b> | <b>100</b>      |
| 1SMB5930BT3            | 930B              | 15.2                   | 16         | 16.8         | 23.4              | 10                                | 600                               | 0.25                            | 1               | 12.2        | 93              |
| <b>1SMB5931BT3</b>     | <b>931B</b>       | <b>17.1</b>            | <b>18</b>  | <b>18.9</b>  | <b>20.8</b>       | <b>12</b>                         | <b>650</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>13.7</b> | <b>83</b>       |
| 1SMB5932BT3            | 932B              | 19                     | 20         | 21           | 18.7              | 14                                | 650                               | 0.25                            | 1               | 15.2        | 75              |
| 1SMB5933BT3            | 933B              | 20.9                   | 22         | 23.1         | 17                | 17.5                              | 650                               | 0.25                            | 1               | 16.7        | 68              |
| <b>1SMB5934BT3</b>     | <b>934B</b>       | <b>22.8</b>            | <b>24</b>  | <b>25.2</b>  | <b>15.6</b>       | <b>19</b>                         | <b>700</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>18.2</b> | <b>62</b>       |
| <b>1SMB5935BT3</b>     | <b>935B</b>       | <b>25.65</b>           | <b>27</b>  | <b>28.35</b> | <b>13.9</b>       | <b>23</b>                         | <b>700</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>20.6</b> | <b>55</b>       |
| <b>1SMB5936BT3, G*</b> | <b>936B</b>       | <b>28.5</b>            | <b>30</b>  | <b>31.5</b>  | <b>12.5</b>       | <b>28</b>                         | <b>750</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>22.8</b> | <b>50</b>       |
| 1SMB5937BT3, G*        | 937B              | 31.35                  | 33         | 34.65        | 11.4              | 33                                | 800                               | 0.25                            | 1               | 25.1        | 45              |
| <b>1SMB5938BT3</b>     | <b>938B</b>       | <b>34.2</b>            | <b>36</b>  | <b>37.8</b>  | <b>10.4</b>       | <b>38</b>                         | <b>850</b>                        | <b>0.25</b>                     | <b>1</b>        | <b>27.4</b> | <b>41</b>       |
| 1SMB5939BT3            | 939B              | 37.05                  | 39         | 40.95        | 9.6               | 45                                | 900                               | 0.25                            | 1               | 29.7        | 38              |
| 1SMB5940BT3            | 940B              | 40.85                  | 43         | 45.15        | 8.7               | 53                                | 950                               | 0.25                            | 1               | 32.7        | 34              |
| 1SMB5941BT3            | 941B              | 44.65                  | 47         | 49.35        | 8                 | 67                                | 1000                              | 0.25                            | 1               | 35.8        | 31              |
| 1SMB5942BT3            | 942B              | 48.45                  | 51         | 53.55        | 7.3               | 70                                | 1100                              | 0.25                            | 1               | 38.8        | 29              |
| 1SMB5943BT3, G*        | 943B              | 53.2                   | 56         | 58.8         | 6.7               | 86                                | 1300                              | 0.25                            | 1               | 42.6        | 26              |
| 1SMB5944BT3            | 944B              | 58.9                   | 62         | 65.1         | 6                 | 100                               | 1500                              | 0.25                            | 1               | 47.1        | 24              |
| 1SMB5945BT3            | 945B              | 64.6                   | 68         | 71.4         | 5.5               | 120                               | 1700                              | 0.25                            | 1               | 51.7        | 22              |
| 1SMB5946BT3            | 946B              | 71.25                  | 75         | 78.75        | 5                 | 140                               | 2000                              | 0.25                            | 1               | 56          | 20              |
| 1SMB5947BT3            | 947B              | 77.9                   | 82         | 86.1         | 4.6               | 160                               | 2500                              | 0.25                            | 1               | 62.2        | 18              |
| 1SMB5948BT3            | 948B              | 86.45                  | 91         | 95.55        | 4.1               | 200                               | 3000                              | 0.25                            | 1               | 69.2        | 16              |
| <b>1SMB5949BT3</b>     | <b>949B</b>       | <b>95</b>              | <b>100</b> | <b>105</b>   | <b>3.7</b>        | <b>250</b>                        | <b>3100</b>                       | <b>0.25</b>                     | <b>1</b>        | <b>76</b>   | <b>15</b>       |
| 1SMB5950BT3            | 950B              | 104.5                  | 110        | 115.5        | 3.4               | 300                               | 4000                              | 0.25                            | 1               | 83.6        | 13              |
| 1SMB5951BT3, G*        | 951B              | 114                    | 120        | 126          | 3.1               | 380                               | 4500                              | 0.25                            | 1               | 91.2        | 12              |
| 1SMB5952BT3            | 952B              | 123.5                  | 130        | 136.5        | 2.9               | 450                               | 5000                              | 0.25                            | 1               | 98.8        | 11              |
| 1SMB5953BT3, G*        | 953B              | 142.5                  | 150        | 157.5        | 2.5               | 600                               | 6000                              | 0.25                            | 1               | 114         | 10              |
| 1SMB5954BT3            | 954B              | 152                    | 160        | 168          | 2.3               | 700                               | 6500                              | 0.25                            | 1               | 121.6       | 9               |
| 1SMB5955BT3            | 955B              | 171                    | 180        | 189          | 2.1               | 900                               | 7000                              | 0.25                            | 1               | 136.8       | 8               |
| 1SMB5956BT3            | 956B              | 190                    | 200        | 210          | 1.9               | 1200                              | 8000                              | 0.25                            | 1               | 152         | 7               |

2. **TOLERANCE AND TYPE NUMBER DESIGNATION** The type numbers listed indicate a tolerance of ±5%.

### 3. ZENER VOLTAGE (V<sub>Z</sub>) MEASUREMENT

Nominal Zener voltage is measured with the device junction in thermal equilibrium with ambient temperature at 25°C.

4. **ZENER IMPEDANCE (Z<sub>Z</sub>) DERIVATION** Z<sub>YT</sub> and Z<sub>ZK</sub> are measured by dividing the ac voltage drop across the device by the ac current applied. The specified limits are for I<sub>Z(ac)</sub> = 0.1 I<sub>Z(dc)</sub> with the ac frequency = 60 Hz.

\* The "G" suffix indicates Pb-Free package available.

# 1SMB5913BT3 Series




Figure 1. Steady State Power Derating




Figure 2. Maximum Surge Power




Figure 3. Zener Voltage - To 12 Volts




Figure 4. Zener Voltage - 14 To 200 Volts




Figure 5.  $V_Z = 3.3$  thru 10 Volts




Figure 6.  $V_Z = 12$  thru 82 Volts

# 1SMB5913BT3 Series




Figure 7. Effect of Zener Voltage




Figure 8. Effect of Zener Current

## Rating and Typical Characteristic Curves ( $T_A = 25^\circ C$ )




Figure 9. Capacitance Curve




Figure 10. Typical Pulse Rating Curve




Figure 11. Pulse Waveform





Figure 12. Pulse Waveform

# 1SMB5913BT3 Series

## OUTLINE DIMENSIONS

**SMB**  
**DO-214AA**  
CASE 403A-03  
ISSUE D




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. D DIMENSION SHALL BE MEASURED WITHIN DIMENSION P.

| DIM | INCHES |        | MILLIMETERS |       |
|-----|--------|--------|-------------|-------|
|     | MIN    | MAX    | MIN         | MAX   |
| A   | 0.160  | 0.180  | 4.06        | 4.57  |
| B   | 0.130  | 0.150  | 3.30        | 3.81  |
| C   | 0.075  | 0.095  | 1.90        | 2.41  |
| D   | 0.077  | 0.083  | 1.96        | 2.11  |
| H   | 0.0020 | 0.0060 | 0.051       | 0.152 |
| J   | 0.006  | 0.012  | 0.15        | 0.30  |
| K   | 0.030  | 0.050  | 0.76        | 1.27  |
| P   | 0.020  | REF    | 0.51        | REF   |
| S   | 0.205  | 0.220  | 5.21        | 5.59  |

## SOLDERING FOOTPRINT\*



SCALE 8:1 (mm/inches)

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERM/D.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 61312, Phoenix, Arizona 85062-1312 USA  
**Phone:** 480-829-7710 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 480-829-7709 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada

**Japan:** ON Semiconductor, Japan Customer Focus Center  
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051  
**Phone:** 81-3-5773-3850

**ON Semiconductor Website:** <http://onsemi.com>

**Order Literature:** <http://www.onsemi.com/litorder>

For additional information, please contact your local Sales Representative.