




- 1 0.00203 [.000080] MIN BRIGHT TIN-LEAD OVER 0.00127 [.000050] MIN NICKEL.
- 2 0.00330 [.000130] MAX PRE-TIN.
- 3 0.00013 [.000005] GOLD OVER 0.00127 [.000050] MIN NICKEL ALL OVER AND 0.00076 [.000030] MIN GOLD ON CONTACT AREA.
- 4 WIRE RANGE: 0.2-0.9mm² (24-18 AWG). INSULATION RANGE: 2.79 [.110] DIA MAX.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 0.00013 [.000005] GOLD OVER 0.00127 [.000050] MIN NICKEL ALL OVER AND 0.00038 [.000015] MIN GOLD ON CONTACT AREA.
- 7 0.00203 [.000080] MIN BRIGHT TIN OVER 0.00127 [.000050] MIN NICKEL.

—	7	3-350980-1
—	6	350980-4
SEE 770258-1	3	350980-3
—	2	350980-2
SEE 640707-1	1	350980-1
LOOSE PIECE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 11-2-92	TE Connectivity			
DIMENSIONS: INCHES		CHK R. SWING 11-2-92				
		APVD E. BEILES 11-2-92	NAME RECEPTACLE, SL-156			
		PRODUCT SPEC	—			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	—			
0 PLC ± -		—	SIZE A2			
1 PLC ± -		—	CAGE CODE 00779			
2 PLC ± 0.13 [.005]		—	DRAWING NO C-350980			
3 PLC ± -		—	RESTRICTED TO —			
4 PLC ± -		—	SCALE 5:1			
ANGLES ± -		—	SHEET 1 of 1			
FINISH		—	REV R2			
MATERIAL 0.33 [.013] BRASS		SEE TABLE	CUSTOMER DRAWING			