





	1	2	3	4	5	6	7																																																																									
A	NOTES: MATERIAL 1.Item Ø Contact pin: Brass(CuZn)Tin plated 2.Item Ø Insulator (housing):Thermoplastic (UL 94V-0),green ELECTRICAL 1.Current Rating : 20A 2.Voltage Rating : 300V 3.Withstand Voltage : 1.6KV ENVIRONMENTAL 1.Soldering Temperature: 250°C ±10°C/5 Sec 2.Operating Temperature: -40°C to +115°C 3.Safety approval: cULus							A																																																																								
B								B																																																																								
C								C																																																																								
D								D																																																																								
E	 Recommended PCB Layout							E																																																																								
F								F																																																																								
G	RoHS compliant  File No.: E349947 <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td>Customer-No.</td><td></td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td>Drawn</td><td>19.03.2009</td><td>Dean</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td>Approved</td><td>19.04.2016</td><td>Winnie</td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±1°</td><td>②</td><td>Drawn</td><td></td><td></td><td>19.04.2016</td><td>Winnie</td></tr><tr><td>X.X°</td><td>±X°</td><td>①</td><td>Drawn</td><td></td><td></td><td>19.03.2009</td><td>Dean</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td></td><td></td><td>Date</td><td>Name</td></tr></table>							Scale	1:1					Customer-No.		TOLERANCE						Date	Name	X.	±0.50				Drawn	19.03.2009	Dean	X.X	±0.30				Approved	19.04.2016	Winnie	X.XX	±0.10							DIM	TOL							X.°	±1°	②	Drawn			19.04.2016	Winnie	X.X°	±X°	①	Drawn			19.03.2009	Dean	Angle	TOL	Id.	Modification			Date	Name	G
Scale	1:1					Customer-No.																																																																										
TOLERANCE						Date	Name																																																																									
X.	±0.50				Drawn	19.03.2009	Dean																																																																									
X.X	±0.30				Approved	19.04.2016	Winnie																																																																									
X.XX	±0.10																																																																															
DIM	TOL																																																																															
X.°	±1°	②	Drawn			19.04.2016	Winnie																																																																									
X.X°	±X°	①	Drawn			19.03.2009	Dean																																																																									
Angle	TOL	Id.	Modification			Date	Name																																																																									
H	<table><tr><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>  ASSMANN WSW-No. A-TB762-0QXXCV Drawing-No. ASS 3419 CO rev02 Replace Sheet							1	2	3	4	5	6	7								H																																																										
1	2	3	4	5	6	7																																																																										
SV1387																																																																																