





PART NUMBER	NO. OF MOD.
10026155-005	1
10026155-005LF	






NOTES:

- ① BODY MATERIAL: LIQUID CRYSTAL POLYMER 30% GLASS.
FLAME RETARDANT ACC. TO UL 94-V0.
COLOR: NATURAL
2. FOR LEAD FREE NUMBERS, ADD AN 'LF' SUFFIX. PART NUMBERS THAT DO NOT END IN 'LF' ARE LEAD FREE.
EXAMPLE: 10026155-005LF
3. THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF AND THE NONE LF PART NUMBERS MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
4. ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOUR PHASE REFLOW OVEN.



mat'l. code SEE NOTE 1				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family METRAL (tm)								
ltr	ecn no	dr	date	tolerances unless otherwise specified						title								
A	V03-0335	LP	03/21/03	angles linear	.X±.3				MM		4 ROW SHROUD							
B	V03-0439	LP	4/22/03		.XX±.13													
C	V06-0080	JRV	3/15/06		.XXX±.051													
D	V06-0609	DCH	2008-06-22	dr	L.POTTEIGER	03/21/03			dwg no						sheet 1 of 2		size	
				enrg	M.GRAY	03/21/03												
				chr	M.GRAY	03/21/03												
				appd	M.GRAY	03/21/03												
sheet index		revision sheet		D	D													
				1	2													

PART NUMBER	DIM A	DIM B	NO. OF MOD.
10026155-001	35.95	34.00	3
10026155-002	23.95	22.00	2
10026155-003	47.95	46.00	4
10026155-004	95.95	94.00	8
10026155-001LF	35.95	34.00	3
10026155-002LF	23.95	22.00	2
10026155-003LF	47.95	46.00	4
10026155-004LF	95.95	94.00	8



mat'l. code	SEE NOTE 1	surface	ASME Y14.5	tolerance	ASME Y14.5	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified			METRAL (tm)
D				angles	.X±.3	MM	4 ROW SHROUD
				0°±2°	.XX±.13	scale 1:1	
				dr	L.POTTEIGER 03/21/03		dwg no
				enr	M.GRAY 03/21/03		sheet 2 of
				chr	M.GRAY 03/21/03		10026155
				app	M.GRAY 03/21/03		size
sheet	revision						A4
index	sheet						type
							CUSTOMER Drawing