

developer.intel.com

intel®

# IXF1002 Dual-Port Gigabit Ethernet MAC

## Product Highlights

- Two full-duplex independent 1-Gbps MACs
- GMII or GPCS physical layer interface
- VLAN tags: add/strip/replace on transmit
- IEEE 802.3x and 802.3z compatible for auto-negotiation and flow control
- 30 to 80 MHz IX Bus speed (5.12 Gbps @ 80 MHz)
- 8-bit or 16-bit CPU interface
- Handles SNMP and RMON counters
- Independent 4-Kbyte Rx FIFO and 2-Kbyte Tx FIFO for each MAC
- 304-pin BGA package
- Low-power 3.3V with 5V tolerance CMOS device

## Product Description

Gigabit Ethernet technology in server and high-end desktop PC network environments is being accelerated by the introduction of Gigabit Ethernet copper PHY (Physical Layer) devices. At the same time, the expanding Internet economy requires shorter design cycles to meet the continuing demand for value-added features. New blades for existing chassis-based routers and switches have a fixed form-factor and limited power budgets. At the same time, designers must meet the demand for increased port density. The IXF1002 dual-port Gigabit Ethernet MAC provides the ideal solution for these design requirements, enabling faster time-to-market, with reduced development costs. For network switch vendors, the IXF1002 dual-port Gigabit Ethernet MAC provides a gigabit Ethernet uplink for 10/100 Mbps switches.

The IXF1002 is the industry's first integrated solution of its kind for router and switch applications. The IXF1002 integrates two MAC



ports to simplify board design, while helping to reduce board real estate requirements, power dissipation, and overall solution cost. In addition, it enhances system performance by implementing programmable features in hardware to offload tasks from the switch or router engine. Both unidirectional and bi-directional IX Bus modes provide options for implementing a variety of switch system architectures. Unique features such as VLAN tag replace, strip, add capability, and header pre-processing enable the IXF1002 to offload tasks from the switch or router engine. Redundancy is a required feature of Gigabit Ethernet systems. The IXF1002 meets this requirement through the integration of two MACs on one device.

The glueless interface to the IXP1200 Network Processor enables designers to easily build a router engine with Gigabit Ethernet backbone connectivity and then enhance it with a growing family of optional IX bus support peripherals and development tools. These include the IXF1002 dual port gigabit Ethernet MAC and the IXP12DE network processor development environment. Whether used alone in a network system design, or as a companion to the IXP1200 network processor, the IXF1002 simplifies system design and enables glueless Gigabit Ethernet backbone connectivity.

## Features

- Two full-duplex independent 1-Gbps controllers
- Up to 80 MHz IX Bus speed
- IX Bus 32-bit or 64-bit bi-directional and 32-bit unidirectional modes
- VLAN tag, replace, and add capabilities on transmit
- Glueless interface to IXP1200 network processor
- GMII or GPCS physical layer interface
- IEEE 802.3x and 802.3z compatible

## Benefits

- Helps simplify hardware design, reduce board space, reduce time-to-market, reduce risk and power dissipation
- Helps to eliminate data flow bottlenecks
- Implements various architectures and optimizes performance
- Offloads switch/router engine from performing these tasks
- Helps to reduce system development time, system cost, risk, and time-to-market
- Interfaces to gigabit Ethernet standard transceivers
- Supports auto-negotiation and flow-control support

## Intel® Internet Exchange™ (IX) Architecture

The Intel IX architecture is a comprehensive family of feature-rich silicon and software building blocks and tools that accelerate development of powerful, flexible network and communications products.

## Ordering Information

Contact an authorized Intel distributor for complete ordering details.

To order the IXF1002 dual-port Gigabit Ethernet MAC specify part number GCIXF1002EC

## Product Specifications

<b>Power supply</b>	3.3V
<b>Operating temperature range</b>	0°C to 70°C
<b>Storage temperature range</b>	-55°C to 125°C
<b>Power dissipation</b>	3W @ 80 MHz
<b>Package</b>	304-pin ESBGA

## Intel Access

Developer's Site	<a href="http://developer.intel.com/">http://developer.intel.com/</a>
Intel Internet Exchange Architecture Home Page	<a href="http://www.intel.com/IXA">http://www.intel.com/IXA</a>
Other Intel Support: Intel Literature Center	<a href="http://developer.intel.com/design/litcentr/">http://developer.intel.com/design/litcentr/</a> (800) 548-4725 7 a.m. to 7 p.m. CST (U.S. and Canada) International locations please contact your local sales office.
General Information Hotline	(800) 628-8686 or (916) 356-3104 5 a.m. to 5 p.m. PST

Information in this document is provided in connection with Intel products. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Intel's Terms and Conditions of Sale for such products, Intel assumes no liability whatsoever, and Intel disclaims any express or implied warranty, relating to sale and/or use of Intel products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right. Intel products are not intended for use in medical, life saving, or life sustaining applications. Intel may make changes to specifications and product descriptions at any time, without notice.

Designers must not rely on the absence or characteristics of any features or instructions marked "reserved" or "unrefined." Intel reserves these for future definition and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to them.

\*Third-party marks and names are the property of their respective owners.



**UNITED STATES AND CANADA**  
Intel Corporation  
Robert Noyce Bldg.  
2200 Mission College Blvd.  
P.O. Box 58119  
Santa Clara, CA 95052-8119  
USA

**EUROPE**  
Intel Corporation (UK) Ltd.  
Pipers Way  
Swindon  
Wiltshire SN3 1RJ  
UK

**ASIA-PACIFIC**  
Intel Semiconductor Ltd.  
32/F Two Pacific Place  
88 Queensway, Central  
Hong Kong, SAR

**JAPAN**  
Intel Kabushiki Kaisha  
P.O. Box 115 Tsukuba-gakuen  
5-6 Tokodai, Tsukuba-shi  
Ibaraki-ken 305  
Japan

**SOUTH AMERICA**  
Intel Semicondutores do Brazil  
Rue Florida, 1703-2 and CJ22  
CEP 04565-001 Sao Paulo-SP  
Brazil