



Tous droits strictement réservés. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER			SIGNAL					POWER										E1	
		E2	P13	P12	P11	5	4	3	2	1	P10	P9	P8	P7	P6	P5	P4	P3	P2		P1
51915-145-- NOTE 3	D C B A		PA	PA	PA	H	H	H	H	H	PA	PA	PA	PA	PA	PA	PA	PA	PA	PA	PA
						G	G	G	G	G											
						F	F	F	F	F											
						E	E	E	E	E											



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
PA	[1.07]	POWER
H	[N/A]	SIGNAL
G	[N/A]	SIGNAL
F	[N/A]	SIGNAL
E	[N/A]	SIGNAL

mat'l code				SEE NOTE 2				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com			
ltr	ecn no.	dr	date	linear	0.X ±0.3				COPY					title 10P + 20S + 3ACP R/A SOLDER RECEPTACLE					
A	DG07-0492	SH	12/12/07		0.XX ±0.13				projection										
					0.XXX ±0.051														
				angles	0° ±2°								product family PwrBlade						
				dr	Sincere He	12/12/07		scale 1:1											
				engr	Sincere He	12/12/07													
				chr	Gary Hsieh	12/12/07													
				appd	Joseph Hsia	12/12/07						size	dwg no	213					
sheet index		revision sheet		A	A	A	A					A	51915-145	sheet 1 of 4					
		1	2			3	4												

Pro/E

PDM: Rev:A

STATUS:Released

Printed: Dec 20, 2010


Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER


51915-145--
NOTE 3




BROKEN-OUT SECTION A-A
SCALE 2:1




SECTION C-C



BROKEN-OUT SECTION B-B
SCALE 2:1



PARTIAL SECTION E-E

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com		
ltr	ecn no.	dr	date	linear	0.X ±0.3		COPY		title 10P + 20S + 3ACP R/A SOLDER RECEPTACLE	
A					0.XX ±0.13		projection 			
					0.XXX ±0.051					
				angles	0° ±2°					
				dr	Sincere He	12/12/07				
				engr	Sincere He	12/12/07	product family PwrBlade			code 213
				chr	Gary Hsieh	12/12/07	size dwg no			sheet
				appd	Joseph Hsia	12/12/07	scale 1:1		2 of 4	
sheet index	revision sheet									

Pro/E

PDM: Rev:A

STATUS: Released

Printed: Dec 20, 2010

All rights reserved.
 Form W-9
 Property

Printed: Dec 20, 2010

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER

51915-145--
NOTE 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
- PLATING:
51915-145, 51915-145LF PLATING SPEC. WAS SHOWN IN THE PRINT OF 10064183.
- MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.
- PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
- PACKAGED IN TRAYS.

PCB NOTES:

- ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
- $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER 0.03
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm 0.07$ HOLE.
- "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
- CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
ltr	ecr no.	dr	date	linear	$0.X \pm 0.3$		COPY		title		
A					$0.XX \pm 0.13$		projection		10P + 20S + 3ACP R/A SOLDER RECEPTACLE		
				angles	$0.XXX \pm 0.051$						
					$0^\circ \pm 2^\circ$						
				dr	Sincere He	12/12/07	scale		product family		code
				engr	Sincere He	12/12/07	1:1		PwrBlade		213
				chr	Gary Hsieh	12/12/07			size		sheet
				appd	Joseph Hsia	12/12/07			dwg no		4 of 4
sheet index		revision sheet									

Pro/E

cage code 22526

4

PDM: Rev:A

STATUS:Released

Printed: Dec 20, 2010