



A

B

C


D

A

B

C

D



spec ref -				dr w wadmin		2010/10/31		projection		MM		size A3		scale 10:1	
tolerance std				eng Guo-Min Sun		2014/10/29						ecn no ELX-N-19241-1			
ISO 406				chr -		-									
ISO 1101				appr Feagle Pan		2014/10/29						product family MINITEK		rel level Released	
TOLERANCES UNLESS OTHERWISE SPECIFIED															
surface -				linear		0.X ±0.5				title 2.0MM UNSHROUDED HEADER		dwg no 59132		rev K	
				0.XX ±0.25											
				0.XXX ±0.150											
ISO 1302				angular 0° ±3°		www.fci.com		cat. no. -		Product - Customer Drw		sheet 1 of 2			
BOARD TO BOARD THRU-HOLE															

PRODUCT NUMBER DESCRIPTION :
59132 - X XX - XX - XXX XLF

PLATING
S = 0.38µm GOLD ON CONTACT AREA
0.38µm GOLD ON TAIL
G = 0.76µm GOLD ON CONTACT AREA
0.76µm GOLD ON TAIL
F = 0.20µm GOLD ON CONTACT AREA
0.20µm GOLD ON TAIL
T = 0.76µm GOLD ON CONTACT AREA
2.54µm 100% MATTE TIN ON TAIL
H = GOLD FLASH ON CONTACT AREA
2.54µm 100% MATTE TIN ON TAIL

LEAD FREE (SEE NOTE 11)
RETENTION (SEE NOTES 6 & 10)
R: RETENTIVE LEG
STACKER HEIGHT (SEE NOTE 7)
PACKAGING: - = BAGS
(SEE NOTE 5) U = TUBES
POSITIONS PER ROW = "N"
(02 TO 25)
OMIT FROM PRODUCT NUMBER FOR
LEAD FREE WITH RETENTIVE LEG PRODUCT


NOTES:
1. MATERIAL HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL 94V-0, COLOR BLACK
2. MATERIAL TERMINAL: COPPER ALLOY

PIN STYLE	OAL
22	08.2
24	09.6
26	10.2
28	11.8
30	13.5
32	14.1
34	15.6
36	17.1
38	19.1
40	21.1
42	18.0

③ TO DETERMINE DIMENSIONS:
N=NUMBER OF POSITIONS PER ROW
EX.: 10 POS., N x 2.00 = 20.00 TOTAL POSITIONS
4. 0.9kg MIN. PIN RETENTION IN EITHER DIRECTION.
5. PACKAGING;
(A) STANDARD PACKAGING: IN POLY BAGS.
(B) SPECIAL PACKAGING: IN TUBE.
FOR ALL SPECIAL PACKAGING,FCI MUST BE
CONTACTED FOR AVAILABILITY IN SIZE REQUESTED.
⑥ RETENTION LEG:
2.3kg MAX INSERTION FORCE AND 1 kg MIN RETENTION
FORCE PER RETENTIVE PIN USING 1.57 THICK CIRCUIT
BOARD AND RECOMMENDED HOLE PATTERN. RETENTIVE
LOCATION AT THE DISCRETION OF THE MANUFACTURER.
RETENTION IS TWO PINS PER PART ADJACENT TO ONE
ANOTHER.

⑦ STACK HEIGHT IS DETERMINED BY CUSTOMER APPLICATION
REQUIREMENTS. SPECIFIED IN mm.
EXAMPLE: 3.7mm STACK HEIGHT=59132-XXX-XX-037X.
⑧ POST LENGTH IS DETERMINED BY: (OAL)-(3.00)-(STACK HGT.)
=POST LENGTH.MINIMUM MATING LENGTH TO BE 2.0mm.

⑨ DIM 1.0 APPLIES TO MOLDED SIDE(S) ONLY. IF SIDE(S) ARE
BROKEN, DIM 1.5 MAX APPLIES.
⑩. OMIT FROM PRODUCT NUMBER IF FEATURE IS NOT APPLICABLE.
⑪. P/N:59132-XXXLF IS SAME AS P/N:59132-XXX. THE SUFFIX 'LF'
IS ADDED FOR EASY LEAD FREE IDENTIFICATION.
12. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
13. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.
14. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
15. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

dr	w wcadmin	2010/10/31	projection 	MM 	size	A3	scale	5:1
eng	Guo-Min Sun	2014/10/29			ecn no	ELX-N-19241-1		
chr	-	-						
appr	Feagle Pan	2014/10/29	product family		MINITEK		rel level	Released
FCi		title			2.0MM UNSHROUDED HEADER			rev
		BOARD TO BOARD THRU-HOLE			dwg no			K
					59132			
www.fci.com		cat. no.	-	Product - Customer Drw			sheet 2 of 2	

FCI
Copyright FCI.