

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-15-004309	18MAR2015	DW	CW
	A3	ECR-15-007632	25MAY2015	DW	CW
	B	ECR-15-014907	14OCT2015	DL	CW
	B1	ECR-16-015492	09NOV2016	QY	CW

NOTES:


- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40-+125^{\circ}C$
WIRE RANGE: 0.14-4 mm² (26-12 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X10XX000)

注释:


- 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40-+125^{\circ}C$
接线范围: 0.14-4 mm² (26-12 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20300X10XX000)



M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐锁紧力矩1.2Nm




4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm








PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不使用防护外壳时芯件的安装开孔图

TYPE-1, T2050322101-000, WITH TE LOGO
类型-1, T2050322101-000, 带TE LOGO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 11JUN2014	 TE Connectivity		
		CHK Chris Wang 11JUN2014			
		APVD Xiang Xu 11JUN2014	NAME HEE-032-M		
DIMENSIONS: mm		PRODUCT SPEC 108-106137	SIZE A300779		
		APPLICATION SPEC 114-106137			
MATERIAL -		WEIGHT -	CAGE CODE T2050322101000		
		Customer Drawing	RESTRICTED TO -		
		SCALE 1:1	SHEET 1 OF 2		REV B1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




NOTE:
ALL SPEC REFER TO TYPE I

注释:
所有产品规范参照 TYPE I

TYPE-2,T2050322101-001,WITH STAINLESS STEEL SCREW,WITHOUT LOGO
类型-2,T2050322101-001,带不锈钢螺丝,无LOGO

T2050322101-001	HEE-032-M	HEE-032 MALE INSERT, WITH STAINLESS STEEL SCREW,WITHOUT LOGO HEE-032 公插,带不锈钢螺丝,无LOGO	TYPE-2 类型-2
T2050322101-000	HEE-032-M	HEE-032 MALE INSERT HEE-032 公插	TYPE-1 类型-1
PART NUMBER 料号	PART DESCRIPTION 描述		TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 11JUN2014	 TE Connectivity					
		CHK Chris Wang 11JUN2014						
DIMENSIONS: mm		APVD Xiang Xu 11JUN2014	NAME HEE-032-M					
		PRODUCT SPEC 108-106137	SIZE A3					
		APPLICATION SPEC 114-106137					CAGE CODE 00779	
		WEIGHT -					DRAWING NO C-T2050322101000	
		RESTRICTED TO -						
MATERIAL - -		FINISH - -	SCALE 1:1					
		Customer Drawing	SHEET 2		OF 2	REV B1		