



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
8/11/07	C	Updated specifications	T.B.	B.S.	
10/12/07	D	Updated dim. for pcb layout	T.B.	B.S.	
6/06/08	E	Temperature range was -40°C to +315°C	T.B.	B.S.	
3/07/14	F	positive contact locator pin was in center	T.B.	B.S.	
4/25/14	G	Updated Specification	T.B.	B.S.	



#### SPECIFICATIONS:

- \* Holder material- White, 30% glass reinforced Liquid Crystal Polymer resin, UL File No. E123598, UL94V-0
- \* Contacts : STAINLESS STEEL 301, spring temper, Gold Flash overall
- \* Temperature range: -40°C to +280°C
- \* Vibration Test: 10-50-10 Hz swept in 60 seconds  
X,Y,Z direction: 1 hour each direction
- \* Result: No dislodgement of the cell or damage  
No discontinuity over 10 micro-seconds
- \* Shock Test: Half sine wave acceleration 150G. 6 ms  
3 shock pulses each direction per axis, total of 18 pulses
- \* Result: No evidence of physical damage
- \* ROHS 2 COMPLIANT

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)		Scale	Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title BU2032SM CR2032 SMD BATTERY HOLDER		
Angular ± 3°	Date 4/25/14	Drawing Number BU2032SM-G	