







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-16-005516	25APR2016	DLD	CJS




ISOMETRIC VIEW
SCALE 10:1



SECTION AF-AF
SCALE 20:1



SECTION N-N
SCALE 20:1



2.06 MAX	2.43	1.00	1.96	FIGURE 2		0.75	18	2098165-4	
1.50-1.85	2.23	0.80	1.82	FIGURE 2		0.35-0.50	20-22	2098165-3	
2.06 MAX	2.43	1.00	1.96	FIGURE 1		0.75	18	2098165-2	
1.50-1.85	2.23	0.80	1.82	FIGURE 1		0.35-0.50	20-22	2098165-1	
INSULATION DIAMETER	L	K	J	REELING DIRECTION	FINISH	mm ² AWG		PART NUMBER	
	DIMENSION					WIRE SIZE			
THIS DRAWING IS A CONTROLLED DOCUMENT.					DWN F. KINSEY 16JAN2009		 TE Connectivity		
					CHK F. KINSEY 16JAN2009				
					APVD C. SCHMID 07MAY2009		NAME		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC		CONTACT, FEMALE, 0.64mm CuNiSi, SIDE ORIENTATION Sn PLATE, HIGH FORCE		
mm		0 PLC ± 1 PLC ± 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±			APPLICATION SPEC				
		FINISH			WEIGHT		SIZE CAGE CODE DRAWING NO		RESTRICTED TO
MATERIAL		-			-		A100779C=2098165		
CUSTOMER DRAWING					SCALE 15:1		SHEET 1 OF 1		REV C