


Threading Inserts



- 16 NR ISO inserts are for use with internal threading holders, page 1439
- Available in grade TB35 and two different tip angle types
- TB35 grade is suitable for milling of steel at higher feeds and speeds

Tip Angle	d	l	s	p	Order Code
Metric					
60°	9.52	16.5	3.18	1.00	712-1910
60°	9.52	16.5	3.18	1.25	712-1921
60°	9.52	16.5	3.18	1.50	712-1933
60°	9.52	16.5	3.18	1.75	712-1945
60°	9.52	16.5	3.18	2.00	712-1957
Whitworth					
55°	9.52	16.5	3.18	11	712-2068
55°	9.52	16.5	3.18	12	712-2070
55°	9.52	16.5	3.18	14	712-2081

225123

		Price Each
Mftrs. List No.	Order Code	
6-141A-011	712-1910	
6-141A-012	712-1921	
6-141A-013	712-1933	
6-141A-014	712-1945	
6-141A-015	712-1957	
6-141A-038	712-2068	
6-141A-036	712-2070	
6-141A-033	712-2081	