


Dimensions:mm (In.)

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Life: 500,000 cycles
- Contact resistance: 100m Ω max.
- Insulation resistance: 100M Ω min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute

Mechanical Specifications:

- Type: SPST surface mount, tactile
- Operating force: 160 $\pm$ 50g
- Operating temperature: -25 $^{\circ}$ ~+70 $^{\circ}$ C
- Storage temperature: -30 $^{\circ}$ ~+80 $^{\circ}$ C
- Travel: .012 $\pm$.004"(.30 $\pm$.10mm)

Materials:

- Cover: Tin plated steel
- Contacts: Silver clad phosphor bronze
- Terminals: Silver clad brass
- Base: Nylon, black
- Stem: Nylon, brown

Soldering Process:

- Maximum reflow soldering temperature: 240 $^{\circ}$ C for 10 seconds max.

Tactile Switch (SMT)

101-0124

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0124](#)