




PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-0.1 [0.756]
1.25-2.0 [0.049-.079]	19.4-0.1 [0.764]
2.0-3.0 [0.079-.118]	19.8-0.1 [0.780]




PANEL CUTOUT
NOT TO SCALE



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	(ON)
1-1a	OPEN	1-1b


()=MOMENTARY



CIRCUIT: SPDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- RATING: 15A @ 125VAC OR
8A @ 250VAC
- APPROVALS: UL, CSA, NEMKO, SEMKO, FEMKO, DEMKO
- MATERIALS: TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
- ELECTRIC LIFE: 10,000 cycles
- CONTACT RESISTANCE: <20 mILLI-Ohms
- INSULATION RESISTANCE: >1000 Mega-OHM
- DIELECTRIC STRENGTH: >1500 VAC 1 minute



E-SWITCH®

TITLE

R1966H BLK BLK HS

SCALE

1.5:1

DATE

5/3/02

DR

CB

DWG

M301237

REV

B

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

B	12297	REVISED DIMENSION/NOTES	7/9/02	CJB
A	12118	RELEASED FOR PRODUCTION	5/3/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD