







SYMBOL DEFINITION		MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	8	
	LAST NO. USED	10	

DWG STATUS		ZONE		REVISION HISTORY		AUTH	DR	APVD
DATE	STG	REV	N/P	CHG				
22MY00	R	01	-	-	ALL PARTS - REDRAWN TO PD FORMAT: 12048369 MAT'L SPEC WAS R0065644 BLUE, 12129377 MAT'L SPEC WAS R0064366 MD GRV	199739	RH	OMC JA
19AP05	R	02	-	-	2X (13) TYP WAS 2X 13 TYP	267465	JBD	JAA NTM





NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
GM PART NO. 16504049 HEADLAMP BULB (TRADE NO. 9004)
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CAVITIES TO ACCEPT 12077411 TERMINAL OR EQUIVALENT.
CABLE SEAL 12010295
GASKET 12048370
TERMINAL POSITION ASSURANCE LOCK 12048371
- SEE CABLE SEAL AND T.P.A. DRAWINGS FOR COMPATIBLE CABLE O.D. RANGE.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- (2.31X10.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".

12129377	02	AA	-	M3592025 PA66 HS IM GRA MD	8.138
12048369	06	AA	-	M3592008 PA66 HS IM BLU	8.138
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	VOL CM³

DIMENSIONAL RANGE (MM)		CHART	
FROM	TO	>	<
0	20	20	30
20	30	30	70
30	70	70	100
70	100	100	150
100	150	150	200
150	200	200	250
200	250	250	300
250	300	300	400
300	400	400	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.15	±0.2	±0.3	±0.4
±0.5	±0.6	±0.8	±1
±1.2	±1.2	±1.2	±1.2
ANGULAR TOLERANCE 12°			

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)		DISTR CODE	
SEE CHART		D	
UNLESS OTHERWISE SPECIFIED			
PERFECT FORM REQUIRED FOR FEATURES OF SIZE AT MMC. TRUE POSITION TOLERANCES AND RELATED DATUMS APPLY AT CONDITION OF SIZE INDICATED IN FEATURE CONTROL FRAME. ALL OTHER GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY SEPARATELY. SEPARATE TRUE POSITION CALLOUTS MAY BE USED SEPARATELY, REGARDLESS OF DATUM REFERENCE.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	
			

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
OR	DATE
APVD1 R. HERMOSILLO	22MY00
APVD2 G. MACIAS	12JUN00
APVD3 J. ALVAREZ	16JUN00
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEC. CHART	
DRAWING NAME	
TAXI CONN 2 F M/P 280 SLD	
DRAWING NUMBER	
12052373	
SIZE	SCALE
A0	5:1
FRAME NO	1 OF 1
SHEET NO	3 OF 3
STG	REV
R	02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12048369-B](#)