
# 1.5 A Adjustable Output, Positive Voltage Regulator

The LM317 is an adjustable 3-terminal positive voltage regulator capable of supplying in excess of 1.5 A over an output voltage range of 1.2 V to 37 V. This voltage regulator is exceptionally easy to use and requires only two external resistors to set the output voltage. Further, it employs internal current limiting, thermal shutdown and safe area compensation, making it essentially blow—out proof.

The LM317 serves a wide variety of applications including local, on card regulation. This device can also be used to make a programmable output regulator, or by connecting a fixed resistor between the adjustment and output, the LM317 can be used as a precision current regulator.

### **Features**

- Output Current in Excess of 1.5 A
- Output Adjustable between 1.2 V and 37 V
- Internal Thermal Overload Protection
- Internal Short Circuit Current Limiting Constant with Temperature
- Output Transistor Safe-Area Compensation
- Floating Operation for High Voltage Applications
- Eliminates Stocking many Fixed Voltages
- Available in Surface Mount D<sup>2</sup>PAK-3, and Standard 3-Lead Transistor Package
- NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable
- These are Pb-Free Devices



\*  $C_{in}$  is required if regulator is located an appreciable distance from power supply filter. \*\*  $C_{O}$  is not needed for stability, however, it does improve transient response.

$$V_{out} = 1.25 V \left( 1 + \frac{R_2}{R_1} \right) + I_{Adj} R_2$$

Since  $I_{Adj}$  is controlled to less than 100  $\mu\text{A},$  the error associated with this term is negligible in most applications.

Figure 1. Standard Application




## ON Semiconductor®

www.onsemi.com



D<sup>2</sup>PAK-3 D2T SUFFIX CASE 936

Heatsink surface (shown as terminal 4 in case outline drawing) is connected to Pin 2.



Heatsink surface connected to Pin 2.

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 10 of this data sheet.

## **DEVICE MARKING INFORMATION**

See general marking information in the device marking section on page 10 of this data sheet.

### **MAXIMUM RATINGS**

Rating		Value	Unit	
Input-Output Voltage Differential	V <sub>I</sub> –V <sub>O</sub>	-0.3 to 40	Vdc	
Power Dissipation Case 221A				
T <sub>A</sub> = +25°C Thermal Resistance, Junction–to–Ambient Thermal Resistance, Junction–to–Case Case 936 (D <sup>2</sup> PAK–3)	P <sub>D</sub> θ <sub>JA</sub> θ <sub>JC</sub>	Internally Limited 65 5.0	W °C/W °C/W	
T <sub>A</sub> = +25°C Thermal Resistance, Junction–to–Ambient Thermal Resistance, Junction–to–Case	P <sub>D</sub> θ <sub>JA</sub> θ <sub>JC</sub>	Internally Limited 70 5.0	°C/W	
Operating Junction Temperature Range	TJ	-55 to +150	°C	
Storage Temperature Range	T <sub>stg</sub>	-65 to +150	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

## **ELECTRICAL CHARACTERISTICS**

 $(V_I - V_O = 5.0 \text{ V}; I_O = 0.5 \text{ A for D2T and T packages}; T_J = T_{low} \text{ to } T_{high} \text{ (Note 1)}; I_{max} \text{ and } P_{max} \text{ (Note 2)}; unless otherwise noted.)}$ 

Characteristics	Figure	Symbol	Min	Тур	Max	Unit
Line Regulation (Note 3), $T_A = +25^{\circ}C$ , $3.0 \text{ V} \leq V_I - V_O \leq 40 \text{ V}$	1	Reg <sub>line</sub>	-	0.01	0.04	%/V
Load Regulation (Note 3), $T_A = +25^{\circ}C$ , 10 mA $\leq I_O \leq I_{max}$ $V_O \leq 5.0 \text{ V}$ $V_O \geq 5.0 \text{ V}$	2	Reg <sub>load</sub>	-	5.0 0.1	25 0.5	mV % V <sub>O</sub>
Thermal Regulation, $T_A = +25^{\circ}C$ (Note 4), 20 ms Pulse	_	Reg <sub>therm</sub>	-	0.03	0.07	% V <sub>O</sub> /W
Adjustment Pin Current	3	$I_{Adj}$	-	50	100	μΑ
Adjustment Pin Current Change, 2.5 V $\leq$ V <sub>I</sub> -V <sub>O</sub> $\leq$ 40 V, 10 mA $\leq$ I <sub>L</sub> $\leq$ I <sub>max</sub> , P <sub>D</sub> $\leq$ P <sub>max</sub>		$\Delta I_{Adj}$	-	0.2	5.0	μΑ
Reference Voltage, 3.0 V $\leq$ V <sub>I</sub> -V <sub>O</sub> $\leq$ 40 V, 10 mA $\leq$ I <sub>O</sub> $\leq$ I <sub>max</sub> , P <sub>D</sub> $\leq$ P <sub>max</sub>	3	$V_{ref}$	1.2	1.25	1.3	V
Line Regulation (Note 3), 3.0 $V \le V_I - V_O \le 40 \text{ V}$	1	Reg <sub>line</sub>	_	0.02	0.07	% V
Load Regulation (Note 3), 10 mA $\leq$ I $_{O} \leq$ I $_{max}$ V $_{O} \leq$ 5.0 V V $_{O} \geq$ 5.0 V	2	Reg <sub>load</sub>	1 1	20 0.3	70 1.5	mV % V <sub>O</sub>
Temperature Stability ( $T_{low} \le T_J \le T_{high}$ )	3	T <sub>S</sub>	_	0.7	_	% Vo
Minimum Load Current to Maintain Regulation (V <sub>I</sub> –V <sub>O</sub> = 40 V)	3	I <sub>Lmin</sub>	-	3.5	10	mA
Maximum Output Current $V_{I}-V_{O} \leq 15 \text{ V, } P_{D} \leq P_{max,} \text{ T Package}$ $V_{I}-V_{O} = 40 \text{ V, } P_{D} \leq P_{max}, T_{A} = +25^{\circ}\text{C, T Package}$	3	I <sub>max</sub>	1.5 0.15	2.2 0.4	_ _	А
RMS Noise, % of $V_O$ , $T_A = +25^{\circ}C$ , 10 Hz $\leq$ f $\leq$ 10 kHz	_	N	_	0.003	_	% V <sub>O</sub>
Ripple Rejection, $V_O$ = 10 V, f = 120 Hz (Note 5) Without $C_{Adj}$ $C_{Adj}$ = 10 $\mu F$	4	RR	- 66	65 80	- -	dB
Thermal Shutdown (Note 6)	_	_	_	180	_	°C
Long–Term Stability, T <sub>J</sub> = T <sub>high</sub> (Note 7), T <sub>A</sub> = +25°C for Endpoint Measurements	3	S	_	0.3	1.0	%/1.0 kHrs.
Thermal Resistance Junction-to-Case, T Package	_	$R_{ heta JC}$	_	5.0	_	°C/W

<sup>1.</sup>  $T_{low}$  to  $T_{high}$  = 0° to +125°C, for LM317T, D2T.  $T_{low}$  to  $T_{high}$  = -40° to +125°C, for LM317BT, BD2T,  $T_{low}$  to  $T_{high}$  = -55° to +150°C, for NCV317BT, BD2T.


<sup>2.</sup> I<sub>max</sub> = 1.5 A, P<sub>max</sub> = 20 W
3. Load and line regulation are specified at constant junction temperature. Changes in V<sub>O</sub> due to heating effects must be taken into account separately. Pulse testing with low duty cycle is used.

<sup>4.</sup> Power dissipation within an IC voltage regulator produces a temperature gradient on the die, affecting individual IC components on the die. These effects can be minimized by proper integrated circuit design and layout techniques. Thermal Regulation is the effect of these temperature gradients on the output voltage and is expressed in percentage of output change per watt of power change in a specified time.

<sup>5.</sup>  $C_{Adj}$ , when used, is connected between the adjustment pin and ground.

Thermal characteristics are not subject to production test.

<sup>7.</sup> Since Long-Term Stability cannot be measured on each device before shipment, this specification is an engineering estimate of average stability from lot to lot.



This device contains 29 active transistors.

Figure 2. Representative Schematic Diagram




Figure 3. Line Regulation and  $\Delta I_{\mbox{\scriptsize Adj}}\mbox{/Line}$  Test Circuit




Figure 4. Load Regulation and  $\Delta I_{\mbox{\scriptsize Adj}}\mbox{/Load Test Circuit}$ 




Figure 5. Standard Test Circuit




Figure 6. Ripple Rejection Test Circuit




Figure 7. Load Regulation




Figure 8. Current Limit




Figure 9. Adjustment Pin Current




Figure 10. Dropout Voltage





Figure 11. Temperature Stability



**Figure 12. Minimum Operating Current** 




Figure 13. Ripple Rejection versus Output Voltage




Figure 14. Ripple Rejection versus
Output Current




Figure 15. Ripple Rejection versus Frequency




Figure 16. Output Impedance




Figure 17. Line Transient Response




Figure 18. Load Transient Response

#### **APPLICATIONS INFORMATION**

## **Basic Circuit Operation**

The LM317 is a 3-terminal floating regulator. In operation, the LM317 develops and maintains a nominal 1.25 V reference ( $V_{ref}$ ) between its output and adjustment terminals. This reference voltage is converted to a programming current ( $I_{PROG}$ ) by  $R_1$  (see Figure 17), and this constant current flows through  $R_2$  to ground.

The regulated output voltage is given by:

$$V_{out} = V_{ref} \left( 1 + \frac{R_2}{R_1} \right) + I_{Adj} R_2$$

Since the current from the adjustment terminal  $(I_{Adj})$  represents an error term in the equation, the LM317 was designed to control  $I_{Adj}$  to less than 100  $\mu A$  and keep it constant. To do this, all quiescent operating current is returned to the output terminal. This imposes the requirement for a minimum load current. If the load current is less than this minimum, the output voltage will rise.

Since the LM317 is a floating regulator, it is only the voltage differential across the circuit which is important to performance, and operation at high voltages with respect to ground is possible.




Figure 19. Basic Circuit Configuration

## **Load Regulation**

The LM317 is capable of providing extremely good load regulation, but a few precautions are needed to obtain maximum performance. For best performance, the programming resistor  $(R_1)$  should be connected as close to the regulator as possible to minimize line drops which effectively appear in series with the reference, thereby degrading regulation. The ground end of  $R_2$  can be returned near the load ground to provide remote ground sensing and improve load regulation.

## **External Capacitors**

A 0.1  $\mu F$  disc or 1.0  $\mu F$  tantalum input bypass capacitor ( $C_{in}$ ) is recommended to reduce the sensitivity to input line impedance.

The adjustment terminal may be bypassed to ground to improve ripple rejection. This capacitor ( $C_{Adj}$ ) prevents ripple from being amplified as the output voltage is increased. A 10  $\mu F$  capacitor should improve ripple rejection about 15 dB at 120 Hz in a 10 V application.

Although the LM317 is stable with no output capacitance, like any feedback circuit, certain values of external capacitance can cause excessive ringing. An output capacitance ( $C_O$ ) in the form of a 1.0  $\mu F$  tantalum or 25  $\mu F$  aluminum electrolytic capacitor on the output swamps this effect and insures stability.

#### **Protection Diodes**

When external capacitors are used with any IC regulator it is sometimes necessary to add protection diodes to prevent the capacitors from discharging through low current points into the regulator.

Figure 18 shows the LM317 with the recommended protection diodes for output voltages in excess of 25 V or high capacitance values ( $C_O > 25~\mu F, \, C_{Adj} > 10~\mu F$ ). Diode  $D_1$  prevents  $C_O$  from discharging thru the IC during an input short circuit. Diode  $D_2$  protects against capacitor  $C_{Adj}$  discharging through the IC during an output short circuit. The combination of diodes  $D_1$  and  $D_2$  prevents  $C_{Adj}$  from discharging through the IC during an input short circuit.




Figure 20. Voltage Regulator with Protection Diodes




Figure 21. D<sup>2</sup>PAK Thermal Resistance and Maximum Power Dissipation versus P.C.B. Copper Length




Figure 22. "Laboratory" Power Supply with Adjustable Current Limit and Output Voltage





Figure 23. Adjustable Current Limiter



 $^{\star}$  D<sub>1</sub> protects the device during an input short circuit.

Figure 24. 5.0 V Electronic Shutdown Regulator




Figure 25. Slow Turn-On Regulator





Figure 26. Current Regulator

## **ORDERING INFORMATION**

Device	Operating Temperature Range	Package	Shipping <sup>†</sup>
LM317BD2TG		D <sup>2</sup> PAK-3 (Pb-Free)	50 Units / Rail
LM317BD2TR4G	T <sub>J</sub> = -40° to +125°C	D <sup>2</sup> PAK-3 (Pb-Free)	800 Tape & Reel
LM317BTG		TO-220 (Pb-Free)	50 Units / Rail
LM317D2TG	T <sub>J</sub> = 0° to +125°C	D <sup>2</sup> PAK-3 (Pb-Free)	50 Units / Rail
LM317D2TR4G		D <sup>2</sup> PAK-3 (Pb-Free)	800 Tape & Reel
LM317TG		TO-220 (Pb-Free)	50 Units / Rail
NCV317BD2TG*	T <sub>J</sub> = -55° to +150°C	D <sup>2</sup> PAK-3 (Pb-Free)	50 Units / Rail
NCV317BD2TR4G*		D <sup>2</sup> PAK-3 (Pb-Free)	800 Tape & Reel
NCV317BTG*		TO-220 (Pb-Free)	50 Units / Rail

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## **MARKING DIAGRAMS**



= Assembly Location

= Wafer Lot
= Year


= Work Week = Pb-Free Package

Α

WL

WW

NC V317BD2T AWLYWWG 317BT AWLYWWG 1 2 3



TO-220


**T SUFFIX** 



<sup>\*</sup>NCV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.

## **PACKAGE DIMENSIONS**

## D<sup>2</sup>PAK-3 **D2T SUFFIX** CASE 936-03 ISSUE E




### NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI
- Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCHES.

- 2. CONTROLLING DIMENSION: INCHES.
  3. TAB CONTOUR OPTIONAL WITHIN
  DIMENSIONS A AND K.
  4. DIMENSIONS U AND V ESTABLISH A MINIMUM
  MOUNTING SURFACE FOR TERMINAL 4.
  5. DIMENSIONS A AND B DO NOT INCLUDE
  MOLD FLASH OR GATE PROTRUSIONS. MOLD
  FLASH AND GATE PROTRUSIONS NOT TO
  EXCEED 0.025 (0.635) MAXIMUM.
  6. SINGLE GAUGE DESIGN WILL BE SHIPPED
  AFTER FEOR EXPIRATION IN OCTOBER 2011.
- AFTER FPCN EXPIRATION IN OCTOBER 2011.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.386	0.403	9.804	10.236	
В	0.356	0.368	9.042	9.347	
С	0.170	0.180	4.318	4.572	
D	0.026	0.036	0.660	0.914	
ED	0.045	0.055	1.143	1.397	
Es	0.018	0.026	0.457	0.660	
F	0.051	REF	1.295	REF	
G	0.100	BSC	2.540	BSC	
Н	0.539	0.579	13.691	14.707	
J	0.125	MAX	3.175	MAX	
K	0.050	REF	1.270 REF		
L	0.000	0.010	0.000	0.254	
M	0.088	0.102	2.235	2.591	
N	0.018	0.026	0.457	0.660	
P	0.058	0.078	1.473	1.981	
R	0°	8°	0°	8°	
S	0.116	REF	2.946 REF		
U	0.200	MIN	5.080 MIN		
V	0.250	MIN	MIN 6.350 MIN		

## **SOLDERING FOOTPRINT\***





\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

### PACKAGE DIMENSIONS

## TO-220, SINGLE GAUGE T SUFFIX CASE 221AB

**ISSUE A** 





- IES:
  DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  CONTROLLING DIMENSION: INCHES.
  DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND
  LEAD IRREGULARITIES ARE ALLOWED.
  PRODUCT SHIPPED PRIOR TO 2008 HAD DIMENSIONS
  S = 0.045 0.055 INCHES (1.143 1.397 MM)

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.570	0.620	14.48	15.75
В	0.380	0.405	9.66	10.28
С	0.160	0.190	4.07	4.82
D	0.025	0.035	0.64	0.88
F	0.142	0.147	3.61	3.73
G	0.095	0.105	2.42	2.66
Н	0.110	0.155	2.80	3.93
J	0.018	0.025	0.46	0.64
K	0.500	0.562	12.70	14.27
L	0.045	0.060	1.15	1.52
N	0.190	0.210	4.83	5.33
Q	0.100	0.120	2.54	3.04
R	0.080	0.110	2.04	2.79
S	0.020	0.024	0.508	0.61
T	0.235	0.255	5.97	6.47

1.27

1.15

0.045

U 0.000 0.050 0.00

0.080

ON Semiconductor and in are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all Claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative