








RECOMMENDED PCB LAYOUT



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
CN	NONE	CN
2-3	OPEN	2-1

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: RATING: 0.4(VA) Max. @20V Max. (AC OR DC)
5. FIXED TERM. & MOVING CONTACT: Cu Alloy w/ GOLD plate.
6. ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to +85°C
10. 2002/95/EC (ROHS) COMPLIANT
11. PACKAGE: TRAY/108 PIECES PER
12. HARDWARE TO BE SUPPLIED IN BULK:
T100011-LOCK WASHER QTY-1
T100015-LOCK RING QTY-1
T100000-HEX NUT QTY-2



TITLE				100SP11B1M7REH		E-SWITCH	
SCALE				2:1		DR TN DWG	
DATE				4/9/07		REV A	
REV.				ECN		TN	
DESCRIPTION				RELEASED FOR PRODUCTION		4/9/07	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				DATE		CHKD	