





DIMENSIONS



TERMINATION



PCB LAYOUT



ORDERING INFORMATION

SERIES	8609	3	96	7	1	13	7	4	5	ELF
ROWS FITTED WITH CONTACTS										
ROW a	b	c	d	e	f	g	h	i	j	k
ROW a	b	c	d	e	f	g	h	i	j	k
NO. OF CONTACTS										
TYPE OF INSULATOR										
3 ROW MALE INSULATOR										
METHOD OF MOUNTING										
STANDARD MOUNTING - STYLE C										
TERMINATION										
ANGLED SPILL										
OPTIONS										
NO. OPTION										
WITH HARPOONS										
PERFORMANCE CLASS										
DIN 4,1612 CLASS 3										
DIN 4,1612 CLASS 2										
DIN 4,1612 CLASS 1										
AS PER MIL C 55302 / JSS 50808										
PITCH PER ROW										
2.54 mm										
LEAD FREE VERSION										
ELF										

GENERAL CHARACTERISTICS & ROHS INFO	
REFER DRAWING C-8609-0000A	

mat'l. code		surface		tolerance		projection		product family	
SEE DRAWING C-8609-0000A		ISO 1302		ISO 406 ISO 1101		Ø		8609	
ltr	ecn	no	dr	ddte	tolerances unless otherwise specified	Ø	mm	title	
A	104-0063	MINI	2004-09-16	angles	0.X	±0.1		DIN STANDARD HEADER	
B	105-0042	MINI	2005-05-19	linear	0.XX	±0.1		DIN 4,1612 STYLE C	
C	106-0061	MINI	2006-05-31	0°±2°	0.XXX	±0.1	scale 3:2		
D	107-0100	KR	2007-08-20	dr	MINI K V	2004-09-16		dwg no	
E	108-0146	KR	2008-10-21	engr	RAKHEE G	2004-09-16		sheet 1 of 1	
				chr	KESAVAN R	2008-10-21		C-8609-2001	
				qppd	KESAVAN R	2008-10-21		type Product Customer Drawing	
sheet index	revision	E	1					size	
								A3	

